



AOC V4 Q32V4 computer monitor 80 cm (31.5") 2560 x 1440 pixels 2K Ultra HD LED Black

Brand : AOC

Product family: V4

Product code: Q32V4

Product name : Q32V4



Q32V431.5" IPS monitor ensuring a great picture quality with QHD resolution

AOC V4 Q32V4 computer monitor 80 cm (31.5") 2560 x 1440 pixels 2K Ultra HD LED Black:

31.5" IPS monitor ensuring a great picture quality with QHD resolution

In an extremely clean design, the Q32V4 boasts a flat 31.5" IPS display with QHD resolution. This model offers the full package with Adaptive Synch, 75Hz refresh rate, Low Blue Light and Flicker-Free.

AOC V4 Q32V4. Display diagonal: 80 cm (31.5"), Display resolution: 2560 x 1440 pixels, HD type: 2K Ultra HD, Display technology: LED, Display surface: Matt, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). VESA mounting.
Product colour: Black



Display		Ports & interfaces	
Display diagonal *	80 cm (31.5")	Headphone connectivity	3.5 mm
Display resolution *	2560 x 1440 pixels	DC-in jack	✓
HD type *	2K Ultra HD	Ergonomics	
Native aspect ratio *	16:9	VESA mounting *	✓
Display technology *	LED	Panel mounting interface	100 x 100 mm
Panel type *	IPS	Cable lock slot *	✓
LED backlight	✓	Cable lock slot type	Kensington
Backlight type	W-LED	Height adjustment *	✗
Touchscreen *	✗	Pivot	✗
Display brightness (typical)	250 cd/m²	Tilt adjustment	✓
Response time *	4 ms	Tilt angle range	-5 - 23°
Response time measurement type	GTG (Gray to Gray)	On Screen Display (OSD)	✓
Display surface	Matt	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Croatian, Polish, Portuguese, Russian, Spanish, Swedish, Turkish, Ukrainian
Anti-glare screen	✓		
Screen shape *	Flat	Number of OSD languages	16
Supported graphics resolutions	1920 x 1080 (HD 1080), 2560 x 1440	Plug and Play	✓
Supported video modes	1080p, 1440p	Power	
Aspect ratio	4:3, 16:9	Energy efficiency class (SDR) *	F
Contrast ratio (typical) *	1000:1	Energy efficiency class (HDR) *	F
Contrast ratio (dynamic)	20000000:1	Energy consumption (SDR) per 1000 hours *	32 kWh
Maximum refresh rate *	75 Hz	Energy consumption (HDR) per 1000 hours *	32 kWh
Viewing angle, horizontal	178°	Power consumption (typical) *	47 W
Viewing angle, vertical	178°	Power consumption (standby) *	0.5 W
Display number of colours *	16.7 million colours		
Pixel density	93 ppi		
Display diagonal (metric)	80.01 cm		
Surface hardness	3H		
Colour depth	8 bit		

Display		Power	
sRGB coverage (typical)	102%	Power consumption (off)	0.3 W
Adobe RGB coverage	75%	AC input voltage	100 - 240 V
Performance		AC input frequency	50/60 Hz
NVIDIA G-SYNC *	✗	Power supply type	Internal
AMD FreeSync *	✗	Energy efficiency scale	A to G
Fast charging	✗	External power adapter	✗
VESA Adaptive Sync support	✓	Weight & dimensions	
Flicker-free technology	✓	Width (with stand)	730.2 mm
Low Blue Light technology	✓	Depth (with stand)	209.9 mm
Multimedia		Height (with stand)	531.1 mm
Number of speakers	2	Weight (with stand)	6.8 kg
RMS rated power	4 W	Width (without stand)	730.2 mm
Built-in speaker(s) *	✓	Depth (without stand)	47.5 mm
Built-in microphone	✗	Height (without stand)	426.6 mm
Built-in camera *	✗	Packaging data	
Design		Package width	817 mm
Market positioning *	Home	Package depth	187 mm
Product colour *	Black	Package height	552 mm
Frameless design	✓	Package weight	8.68 kg
Front bezel colour	Black	Package type	Box
Detachable stand	✓	Packaging content	
Feet colour	Black	Stand included	✓
Ports & interfaces		Cables included	AC, HDMI
Built-in USB hub *	✗	Quick start guide	✓
DVI port	✗	HDMI cable length	1.5 m
HDMI *	✓	Sustainability	
HDMI ports quantity	1	Doesn't contain	Mercury, PVC/BFR
HDMI version	1.4	Other features	
DisplayPorts quantity	1	Exterior finish type	Textured
DisplayPort version	1.2	Bezel thickness type	Narrow
Audio input	✓	Warranty period	3 year(s)
Headphone out *	✓	Compliance certificates	WEEE
Headphone outputs	1	Light effects	✗
		Certification	WEEE,REACH compliant,RoHs compliant,CB,Microsoft WHQL
		Logistics data	
		Harmonized System (HS) code	85285210



4038986119900

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.