



APC Easy UPS 3M 60kVA 400V 3:3 UPS, 3 internal 9Ah modular battery strings expandable to 6, Start-up 5x8

Brand : APC

Product code: E3MUPS60KHB1S

Product name : Easy UPS 3M 60kVA 400V 3:3 UPS, 3 internal 9Ah modular battery strings expandable to 6, Start-up 5x8

Easy UPS 3M 60kVA 400V 3:3 UPS, 3 internal 9Ah modular battery strings expandable to 6, Start-up 5x8

APC Easy UPS 3M 60kVA 400V 3:3 UPS, 3 internal 9Ah modular battery strings expandable to 6, Start-up 5x8:

Easy-to-install, easy-to-connect, easy-to-use, and easy-to-service 60 kVA 3-phase UPS. With advanced product features, robust electrical specifications and compact design, the Easy UPS 3M UPS makes business continuity easy for small and medium data centers and other business critical applications. Includes 5x8 start-up service and 3 internal 9 Ah modular battery strings, expandable to 6 for extended runtime.



Features		Design	
UPS topology *	Double-conversion (Online)	Product colour *	White
Output power capacity *	60 kVA	International Protection (IP) code	IP20
Output power *	60 W	Operational conditions	
Waveform *	Sine	Operating temperature (T-T)	0 - 40 °C
Input operation voltage (min) *	342 V	Storage temperature (T-T)	-15 - 40 °C
Input operation voltage (max) *	477 V	Operating relative humidity (H-H)	0 - 95%
Input frequency *	40 - 70 Hz	Storage relative humidity (H-H)	0 - 95%
Output operation voltage (min)	380 V	Certificates	
Output operation voltage (max)	415 V	Compliance certificates	RoHS
Output frequency	50/60 Hz	Certification	CE, EAC, IEC 62040-1-1, IEC 62040-2, IEC 62040-3, IEC 62040-4, ISTA 2B, RCM, WEEE
Power factor	0.99	Weight & dimensions	
Output voltage Total Harmonic Distortion (THD)	3%	Width	600 mm
Input current Total Harmonic Distortion (THD)	3%	Depth	1000 mm
Audible alarm(s)	✓	Height	1970 mm
Battery		Weight	311 kg
Battery technology	Sealed Lead Acid (VRLA)	Packaging data	
Battery voltage	240 V	Package width	750 mm
Design		Package depth	1125 mm
Form factor *	Tower	Package height	2102 mm
		Package weight	360 kg
		Logistics data	
		Harmonized System (HS) code	85078000



8592978435578



0731304347170



731304347170

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.