

Viewsonic EP5542T Signage Display Totem design 139.7 cm (55") LED 450 cd/m² 4K Ultra HD Black Touchscreen Android 8.0

Brand : Viewsonic

Product code: EP5542T

Product name : EP5542T

55", TFT LCD, 2160 x 3840, 9:16, 1.07B, HDMI 2.0

Viewsonic EP5542T. Product design: Totem design. Display diagonal: 139.7 cm (55"), Display technology: LED, Display resolution: 2160 x 3840 pixels, Display brightness: 450 cd/m², HD type: 4K Ultra HD, Touchscreen. Operating system installed: Android 8.0. Product colour: Black



Display		Power	
LED backlighting type	Direct-LED	Energy consumption (SDR) per 1000 hours	73 kWh
Display diagonal *	139.7 cm (55")	AC input voltage	100-240 V
Display technology *	LED	AC input frequency	50 - 60 Hz
Display resolution *	2160 x 3840 pixels	Energy efficiency scale	A to G
Display brightness *	450 cd/m ²	Computer system	
HD type *	4K Ultra HD	Computer system *	✓
Touchscreen *	✓	Internal storage capacity	16 GB
Touchscreen technology	Infrared	Operating system installed	Android 8.0
Number of simultaneous touchpoints	10	Video formats supported	AVI, DAT, MKV, MOV, MP4, MPEG, MPG, RM, RMVB, TS, WMV
Multi-touch	✓	Audio formats supported	AAC, MP3, WAV
Native aspect ratio	9:16	Image formats supported	BMP, JPG, PNG
Response time	9 ms	Weight & dimensions	
Contrast ratio (typical)	1300:1	Display width	768.5 mm
Viewing angle, horizontal	178°	Display depth	450 mm
Viewing angle, vertical	178°	Display height	1870 mm
Display number of colours	1.07 billion colours	Display weight	62.7 kg
Active display area (W x H)	1209.6 x 680.4 mm	Weight	58 kg
Panel life	30000 h	Packaging data	
Ports & interfaces		Package width	920 mm
HDMI ports quantity *	3	Package depth	550 mm
HDMI version	2.0	Package height	2000 mm
HDMI input ports quantity	3	Package weight	66.7 kg
DVI port *	✗	Packaging content	
VGA (D-Sub) input ports	1	Remote control included	✓
DisplayPorts quantity *	1	Batteries included	✓
DisplayPorts in	1		
USB port *	✓		

Ports & interfaces		Packaging content	
USB ports quantity	5	Cables included	AC
Ethernet LAN (RJ-45) ports	1	Operational conditions	
PC Audio in	✓	Operating temperature (T-T)	0 - 40 °C
RS-232 interface	✓	Operating relative humidity (H-H)	20 - 80%
Audio		Storage temperature (T-T)	-20 - 60 °C
Built-in speaker(s) *	✓	Storage relative humidity (H-H)	10 - 90%
Number of built-in speakers	2	Certificates	
RMS rated power	20 W	Certification	cTUVus, FCC, Energy Star, CE, CB, RoHS, ErP, EEI, WEEE, BSMI
Design		Logistics data	
Product design *	Totem design	Products per master (outer) case	1 pc(s)
Placement supported *	Indoor	Pallet gross length	92 cm
Product colour *	Black	Pallet gross width	55 cm
Performance		Pallet gross height	2.13 m
Purpose *	Universal	Harmonized System (HS) code	8528529100
Power		Network	
Power consumption (typical) *	126 W	Ethernet LAN *	✓
Power consumption (off)	0.5 W	Wi-Fi *	✗
Energy efficiency class (SDR)	F	Technical details	
		Sustainability certificates	ENERGY STAR, ErP
		Compliance certificates	CE, RoHS



0766907006902



766907006902

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.