APC Battery Replacement Cartridge APCRBC151 (OEM)



Brand : APC

Product code: APCRBC151

Product name : Battery Replacement Cartridge APCRBC151 (OEM)

- "12V 5.1AH replaceable battery for APC Smart-UPS C Line Interactive"
- "Brand new battery shipped from strictly managed warehouse"
- "Peace of mind with 2-year warranty and UPS safety certifications"
- "Supports APC-authorized recycling for earth-friendly disposal"
- "lead-acid battery"

Battery Replacement Cartridge APCRBC151 (OEM)

APC Battery Replacement Cartridge APCRBC151 (OEM):

Genuine APC RBC(TM) are tested and certified for compatibility to restore UPS performance to the original specifications.
APC Battery Replacement Cartridge APCRBC151 (OEM). Battery technology: Sealed Lead Acid (VRLA), Battery voltage: 12 V, Number of batteries included: 1 pc(s). Compliance certificates: RoHS, Certification: REACH. Weight: 10 kg, Width: 216 mm, Height: 83 mm. Package width: 368 mm, Package height: 152 mm, Package depth: 495 mm

Features	
Battery technology *	Sealed Lead Acid (VRLA)
Battery voltage *	12 V
Number of batteries included *	1 pc(s)
Battery life	5 year(s)
Product colour	Metallic
Certificates	
Compliance certificates	RoHS
Certification	REACH
Weight & dimensions	
Weight	10 kg
Width	216 mm
Height	83 mm
Depth	343 mm
Packaging data	
Package width	368 mm

Packaging data	
Package height	152 mm
Package depth	495 mm
Package weight	10.9 kg
Package weight	10.91 kg
Operational conditions	
Operating temperature (T-T)	0 - 45 °C
Storage temperature (T-T)	-15 - 40 °C
Operating relative humidity (H-H)	0 - 95%
Storage relative humidity (H-H)	0 - 95%
Operating altitude	0 - 3000 m
Non-operating altitude	0 - 15000 m
Logistics data	
Harmonized System (HS) code	85044095

0731304310150

731304310150

0731304310150

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date