

Neomounts floor stand

Brand : Neomounts

Product code: PLASMA-M1700ES

Product name : Neomounts floor stand

32-70", 147.5 - 163.5 cm, max 50 kg

Neomounts floor stand. Maximum weight capacity: 50 kg, Minimum screen size: 81.3 cm (32"), Maximum screen size: 177.8 cm (70"), Minimum VESA mount: 200 x 200 mm, Maximum VESA mount: 600 x 450 mm. Height adjustment range: 1475 - 1635 mm, Tilt angle range: 0 - 20°. Product colour: Black



Mounting		Weight & dimensions	
Maximum weight capacity *	50 kg	Height	1635 mm
Minimum screen size	81.3 cm (32")	Weight	34.9 kg
Number of displays supported *	1	Packaging data	
Maximum weight capacity (per display) *	50 kg	Package width	345 mm
Maximum screen size *	177.8 cm (70")	Package depth	135 mm
Mounting type *	Floor	Package height	1170 mm
Minimum VESA mount *	200 x 200 mm	Package weight	13 kg
Maximum VESA mount *	600 x 450 mm	Other features	
Panel mounting interface	200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400, 400 x 600, 600 x 400, 600 x 600, 600 x 800	Country of origin	China
		Logistics data	
		Master (outer) case net weight	12 kg
		Harmonized System (HS) code	9403109800
Ergonomics		Products per pallet (EU)	14 pc(s)
Height adjustment type	Manual	Master (outer) case width	345 mm
Height adjustment range	1475 - 1635 mm	Master (outer) case length	135 mm
Tilt angle range	0 - 20°	Master (outer) case height	1170 mm
Design		Master (outer) case gross weight	13 kg
Type	Fixed floor stand		
Product colour *	Black		



8717371445140

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.