

Targus Click-In 26.7 cm (10.5") Folio Silver

Brand : Targus
Product code: THZ85011GL
Product name : Click-In

Click-In, 10.5", iPad (7th gen.) 10.2/iPad Air 10.5/iPad Pro 10.5, PU, TPU, Silver

Targus Click-In 26.7 cm (10.5") Folio Silver:

Wrap your iPad® (7th gen.) 10.2-inch in strong, military grade drop protection*. Engineered for durability without adding weight, the Targus Click-In™ Case features a flexible tray with wrap-around bezel and reinforced corners to ward off bumps and dings.

The tray also flexes to fit iPad Air® 10.5-inch and iPad Pro® 10.5-inch for a snug, safe fit. It is structurally designed to redirect sound for enhanced audio. Precision cutouts give full access to controls, ports and cameras. Enjoy added efficiency with an integrated loop for your Apple Pencil® or stylus.

The structured cover is engineered to protect, while a non-slip interior makes it easy to adjust your device into infinite viewing angles or a comfortable typing position. Altogether, it's a superior choice for protecting your tablet.



Features		Packaging data	
Compatibility *	iPad (7th gen.) 10.2 iPad Air 10.5 iPad Pro 10.5	Package depth	187.9 mm
Maximum screen size *	26.7 cm (10.5")	Package height	291 mm
Case type *	Folio	Package weight	440 g
Material *	Polyurethane, Thermoplastic polyurethane (TPU)	Logistics data	
Product main colour *	Silver	Harmonized System (HS) code	84733080
Brand compatibility *	Apple	Shipping (inner) case width	13.1 cm
Closure type	Strap closure	Shipping (inner) case length	20.1 cm
Built-in speaker(s) *	✗	Shipping (inner) case height	30.7 cm
Stand mode *	✓	Products per shipping (inner) case	5 pc(s)
Protection features	Bump resistant	Master (outer) case width	281 mm
Battery		Master (outer) case length	420 mm
Built-in battery *	✗	Master (outer) case height	332 mm
Weight & dimensions		Master (outer) case gross weight	9.97 kg
Width	20 mm	Products per master (outer) case	20 pc(s)
Depth	182 mm	Shipping (inner) case net weight	2.34 kg
Height	255 mm	Products per pallet	720 pc(s)
Weight	380 g		
Packaging data			
Package width	25 mm		



5051794029383



0092636344375



092636344375

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.