



DELL Pro Plus Compact Mouse - MS5120W - Titan Gray

Brand : DELL

Product code: MS5120W-GY

Product name : Pro Plus Compact Mouse - MS5120W - Titan Gray

Pro Plus Compact Mouse - MS5120W - Titan Gray

[DELL Pro Plus Compact Mouse - MS5120W - Titan Gray:](#)

Connect your mouse conveniently via 2.4GHz wireless or Bluetooth with any PC and enhance your productivity with programmable shortcut buttons and 36 months of battery life.

DELL Pro Plus Compact Mouse - MS5120W - Titan Gray. Form factor: Ambidextrous. Movement detection technology: Optical, Device interface: RF Wireless + Bluetooth, Movement resolution: 1600 DPI, Buttons type: Pressed buttons, Buttons quantity: 7, Scroll type: Wheel. Power source: Batteries. Product colour: Grey, Titanium



Mouse		System requirements	
Number of scroll wheels	1	Mac operating systems supported	✓
Purpose *	Office	Linux operating systems supported	✓
Device interface *	RF Wireless + Bluetooth	Mobile operating systems supported	Android
Movement detection technology *	Optical	Other operating systems supported	DOS
Movement resolution *	1600 DPI	Operational conditions	
Buttons type	Pressed buttons	Operating temperature (T-T)	-10 - 50 °C
Scroll type *	Wheel	Storage temperature (T-T)	-40 - 65 °C
Programmable mouse buttons	✓	Weight & dimensions	
Buttons quantity *	7	Width	104.5 mm
Number of programmable buttons	2	Depth	61.5 mm
Frequency band	2.4 GHz	Height	38.3 mm
Bluetooth version	5.0	Weight	102 g
Design		Packaging data	
Form factor *	Ambidextrous	Quantity per pack *	1 pc(s)
Product colour *	Grey, Titanium	Package width	86 mm
Surface coloration	Monochromatic	Package depth	47 mm
Ergonomics		Package height	133 mm
Wireless range	10 m	Package weight	184 g
Power		Packaging content	
Power source *	Batteries	Receiver included	✓
Number of batteries supported	1	Wireless receiver interface	USB Type-A
Battery type	AA	Receiver type	Nano receiver
Service life of battery	36 month(s)	Logistics data	
		Harmonized System (HS) code	84716070



5397184289174



5704174391920



0884116366805



884116366805

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.