

ASUS ZenScreen MB16AWP computer monitor 39.6 cm (15.6") 1920 x 1080 pixels Full HD LED Black

Brand : ASUS

Product family: ZenScreen

Product code: 90LM0711-B01370

Product name : MB16AWP



- 15.6-inch FHD display with super-narrow bezels and anti-glare coating
- Effortless wireless mirroring support for iOS, Android, plus Windows 10 and above devices (including Win 11)
- Rich connectivity with two USB Type-C® and mini HDMI® ports, plus an earphone jack
- Two embedded 1-watt speakers with smart amplifier
- Built-in G-sensor enables an Auto Rotation feature that automatically senses display orientation and switches between landscape and portrait modes
- Rear tripod socket is compatible with any standard camera tripod
- Built-in 7800 mAh battery

ASUS ZenScreen Go MB16AWP Wireless Portable Monitor- 15.6 inch, Wireless mirroring, IPS, USB Type-C, mini HDMI, Built-in battery, Flicker Free, Blue Light Filter, Anti-glare surface, Tripod socket



Display		Ports & interfaces	
Display diagonal *	39.6 cm (15.6")	HDMI *	✗
Display resolution *	1920 x 1080 pixels	Mini HDMI ports quantity	1
HD type *	Full HD	Headphone out *	✓
Native aspect ratio *	16:9	Headphone outputs	1
Display technology *	LED	HDCP	✓
Panel type *	IPS	Network	
Backlight type	LED	Wi-Fi	✓
Touchscreen *	✗	Remotely operated	✓
Display brightness (typical)	250 cd/m²	Ergonomics	
Response time *	5 ms	VESA mounting *	✗
Anti-glare screen	✓	Cable lock slot *	✓
Screen shape *	Flat	Cable lock slot type	Kensington
Supported graphics resolutions	1920 x 1080 (HD 1080)	Height adjustment *	✗
Aspect ratio	16:9	Tilt adjustment	✓
Contrast ratio (typical) *	1200:1	Tilt angle range	15 - 75°
Contrast ratio (dynamic)	100000000:1	Power	
Maximum refresh rate *	60 Hz	Energy efficiency class (SDR) *	C
Viewing angle, horizontal	178°	Energy consumption (SDR) per 1000 hours *	8 kWh
Viewing angle, vertical	178°	Power consumption (typical) *	7.6 W
Display number of colours *	16.7 million colours	Power consumption (off)	0.3 W
Pixel pitch	0.179 x 0.179 mm	Input current	3 A
Viewable size, horizontal	34.4 cm	Energy efficiency scale	A to G
Viewable size, vertical	19.4 cm	Weight & dimensions	
Digital horizontal frequency	53 - 77 kHz	Width (with stand)	357.9 mm
Digital vertical frequency	48 - 61 Hz	Depth (with stand)	11.5 mm
sRGB coverage (typical)	100%		
Performance			
NVIDIA G-SYNC *	✗		

Performance		Weight & dimensions	
AMD FreeSync *	✗	Height (with stand)	224.8 mm
Flicker-free technology	✓	Weight (with stand)	1.09 kg
Low Blue Light technology	✓	Packaging data	
Multimedia		Package width	446 mm
Number of speakers	2	Package depth	139 mm
RMS rated power	2 W	Package height	291 mm
Built-in speaker(s) *	✓	Package weight	2.3 kg
Design		Package type	Box
Product colour *	Black	Packaging content	
Ports & interfaces		Cables included	AC, USB Type-C
Built-in USB hub *	✗	Other features	
USB Type-C downstream ports quantity	1	AirPlay	✓
		Battery	
		Battery capacity	7800 mAh
		Logistics data	
		Harmonized System (HS) code	85285210



4711081309451



0195553309486



195553309486



4711081385127



5715328234024

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.