
Lenovo 4XC7A08239 network card Internal Ethernet



Brand : Lenovo

Product code: 4XC7A08239

Product name : 4XC7A08239

ThinkSystem Broadcom 57416 10GBASE-T 2-port OCP Ethernet Adapter

Lenovo 4XC7A08239 network card Internal Ethernet:

The Broadcom 57416 10Gb BASE-T Ethernet Adapters are dual-port 10GBASE-T adapters that are fully compliant with the IEEE 802.3an standard and provide a low-cost solution for 10 Gb Ethernet using copper wiring.
Lenovo 4XC7A08239. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Product colour: Green, Metallic

Ports & interfaces	
Connectivity technology *	Wired
Host interface *	PCI Express
Interface *	Ethernet
Ethernet LAN (RJ-45) ports	4
PCI version	3.0

Network	
Networking standards *	IEEE 802.3ab, IEEE 802.3an
Ethernet LAN	✔
Ethernet interface type	10 Gigabit Ethernet, Gigabit Ethernet
Ethernet LAN data rates	1000,10000 Mbit/s
Cabling technology	10GBase-T

Design	
Component for *	Server
Product colour	Green, Metallic
Internal *	✔

Design	
Form factor	OCP 3.0

System requirements	
Windows operating systems supported	✔
Linux operating systems supported	✔

Operational conditions	
Storage temperature (T-T)	-40 - 65 °C
Storage relative humidity (H-H)	5 - 95%

Weight & dimensions	
Width	76 mm
Depth	115 mm

Logistics data	
Harmonized System (HS) code	85176990



0889488497317



889488497317

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date