



Viewsonic IFP7550-3 interactive whiteboard 190.5 cm (75") 3840 x 2160 pixels Touchscreen Black HDMI

Brand : Viewsonic

Product code: IFP7550-3

Product name : IFP7550-3

75", 3840x2160, TFT LCD, 8ms, 3GB DDR4, 32GB, Android 8, IR Recognition, HDMI, VGA, RS-232, SPDIF, RJ-45, USB, 1710x1020x90 mm

Viewsonic IFP7550-3. Display diagonal: 190.5 cm (75"), Working area: 1666 x 945 mm, Display brightness: 350 cd/m². Operating system installed: Android, Processor architecture: ARM Cortex-A73, Processor frequency: 1.5 GHz. Speaker power: 20 W, Subwoofer RMS power: 15 W. Ethernet LAN data rates: 10,100 Mbit/s. Interface: HDMI, USB connector type: USB Type-A, USB Type-B, Headphone connectivity: 3.5 mm



Display		Ports & interfaces	
Display diagonal *	190.5 cm (75")	USB connector type	USB Type-A, USB Type-B
Display brightness	350 cd/m ²	HDMI ports quantity	3
Display number of colours	1.073 billion colours	HDMI version	2.0
Display resolution	3840 x 2160 pixels	RGB ports quantity	1
HD type	4K Ultra HD	Ethernet LAN (RJ-45) ports	1
Panel type	LCD	OPS slot	1
LED backlighting type	Direct-LED	Headphone connectivity	3.5 mm
Contrast ratio (typical)	1200:1	RS-232 ports	1
Contrast ratio (dynamic)	5000:1	Ergonomics	
Response time	8 ms	Product colour	Black
Touchscreen *	✓	VESA mounting	✓
Touch technology	Multi-touch	Panel mounting interface	800 x 400 mm
Touchscreen type	Infrared	Mean time between failures (MTBF)	30000 h
Number of simultaneous touchpoints	20	Certification	cTUVus, FCC, ES8, EPEAT, EMC/CE, CB, RoHS & DOC, REACH, WEEE, ErP, EAC, UKrSEPRO, RCM, BSMI
Touch resolution	32767 x 32767 pixels	Power	
Touch system response time	10 ms	Power consumption (typical)	138 W
Viewing angle, horizontal	178°	Power consumption (off)	0.5 W
Viewing angle, vertical	178°	AC input voltage	100 - 240 V
Working area *	1666 x 945 mm	Energy efficiency class	G
Computer system		Energy efficiency scale	A to G
Operating system installed	Android	Operational conditions	
Operating system version	8	Operating temperature (T-T)	0 - 40 °C
Built-in processor	✓	Operating relative humidity (H-H)	10 - 90%
Processor architecture	ARM Cortex-A73	Weight & dimensions	
Processor frequency	1.5 GHz	Width *	1710 mm
Processor cores	4	Depth	90 mm
Maximum internal memory	32 GB	Height *	1020 mm
RAM capacity	3 GB	Weight	53.9 kg
RAM type	DDR4	Packaging data	
Audio		Package width	1930 mm
Built-in speaker(s) *	✓		
Number of built-in speakers	2		

Audio		Packaging data	
Speaker power	20 W	Package depth	280 mm
Built-in subwoofer	✓	Package height	1140 mm
Subwoofer RMS power	15 W	Package weight	71.9 kg
Projector		Quantity per pack	1 pc(s)
Built-in projector *	✗	Packaging content	
Network		USB cable length	3 m
Ethernet LAN	✓	Cables included	AC, HDMI, USB
Ethernet LAN data rates	10,100 Mbit/s	Mounting kit	✓
Ports & interfaces		Mounting brackets included	✓
Interface	HDMI	Quick start guide	✓
USB 3.2 Gen 1 (3.1 Gen 1) Type-A hub ports quantity	4	Stylus included	✓
USB 3.2 Gen 1 (3.1 Gen 1) Type-A Touch ports quantity	2	Bundled software	Basic Annotation Software: myViewBoard Pro Annotation Software: myViewBoard for Windows (Embedded in Windows Slot-in PC)
USB 2.0 ports quantity	3		
		Other features	
		Country of origin	China



0766907002478



766907002478

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.