



Canon IRIScan Desk 6 document camera Black, Silver CMOS USB 2.0

Brand : Canon

Product code: 3981V746

Product name : IRIScan Desk 6

- USB-powered, compact, and portable
 - Convert documents and pocket books into digital files to edit and share remotely
 - Scan an A4 colour document in less than 1 second
- A4, 8Mp, CMOS, 3264 x 2448 px, 300 dpi, USB 2.0

Canon IRIScan Desk 6 document camera Black, Silver CMOS USB 2.0:

Supreme efficiency from a portable book and document scanner with advanced image processing
Canon IRIScan Desk 6. Effective sensor resolution: 8 MP, Sensor type: CMOS, Supported graphics resolutions: 3264 x 2448. Interface: USB 2.0. Power supply type: USB, Operating voltage: 5 V. Windows operating systems supported: Windows 10, Windows 8, Windows 7, Windows 11, Mac operating systems supported: Mac OS X 10.14 Mojave, Mac OS X 10.6 Snow Leopard, Mac OS X 13.0 Ventura, Mac OS X 10.15 Catalina,.... Width: 120 mm, Depth: 210 mm, Height: 320 mm



Camera		Power	
Effective sensor resolution *	8 MP	Power supply type *	USB
Sensor type *	CMOS	Operating voltage	5 V
Supported graphics resolutions *	3264 x 2448	System requirements	
Maximum frame rate	15 fps	Windows operating systems supported	Windows 10, Windows 8, Windows 7, Windows 11
Light source	LED		Mac OS X 10.14 Mojave, Mac OS X 10.6 Snow Leopard, Mac OS X 13.0 Ventura, Mac OS X 10.15 Catalina, Mac OS X 10.7 Lion, Mac OS X 14.0 Sonoma, Mac OS X 10.15.3 Catalina, Mac OS X 10.7.5 Lion, Mac OS X 10.2 Jaguar, Mac OS X 10.8 Mountain Lion, Mac OS X 10.11 El Capitan, Mac OS X 10.3 Panther, Mac OS X 10.9 Mavericks, Mac OS X 10.12 Sierra, Mac OS X 10.4 Tiger, Mac OS X 11.0 Big Sur, Mac OS X 10.13 High Sierra, Mac OS X 10.5 Leopard, Mac OS X 12.0 Monterey
Colour depth	24 bit	Mac operating systems supported	
Ports & interfaces			
Interface *	USB 2.0		
Technical details			
Document size (max)	A4		
Product colour *	Black, Silver		
Image formats supported	JPEG		
		Weight & dimensions	
		Width	120 mm
		Depth	210 mm
		Height	320 mm
		Weight	1.05 kg
		Dimensions folded (WxDxH)	120 x 90 x 320 mm



5420079900967

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.