



LG 49WQ95C-W computer monitor 124.5 cm (49") 5120 x 1440 pixels UltraWide Dual Quad HD Silver

Brand : LG

Product code: 49WQ95C-W.AEK

Product name : 49WQ95C-W

- 49-inch UltraWide™ Dual QHD(5120x1440) at 144Hz / Nano IPS™ Display
- DCI-P3 98%(Typ.) / VESA Display HDR™ 400
- USB Type-C™ with 90W Power Delivery
- 2 x 10W Stereo Speaker with Rich Bass
- Eye Care Features
- Height/Tilt/ Swivel Adjustable Stand

49", 5120 x 1440, 32:9, 400 cd/m², DCI-P3 98%, IPS, 3800R

LG 49WQ95C-W. Display diagonal: 124.5 cm (49"), Display resolution: 5120 x 1440 pixels, HD type: UltraWide Dual Quad HD, Response time: 5 ms, Native aspect ratio: 32:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Height adjustment. Product colour: Silver



Display		Ports & interfaces	
Display diagonal *	124.5 cm (49")	HDMI ports quantity	2
Display resolution *	5120 x 1440 pixels	DisplayPorts quantity	1
HD type *	UltraWide Dual Quad HD	Headphone out *	✓
Native aspect ratio *	32:9	Ergonomics	
Panel type *	IPS	Wall mountable	✓
Touchscreen *	✗	Cable lock slot *	✗
Display brightness (typical)	400 cd/m²	Height adjustment *	✓
Response time *	5 ms	Swivelling	✓
Screen shape *	Curved	Tilt adjustment	✓
Screen curvature rating	3800R	Power	
Contrast ratio (typical) *	1000:1	Energy efficiency class (SDR) *	F
Maximum refresh rate *	144 Hz	Energy efficiency class (HDR) *	G
Viewing angle, horizontal	178°	Energy consumption (SDR) per 1000 hours *	45 kWh
Viewing angle, vertical	178°	Energy consumption (HDR) per 1000 hours *	109 kWh
Display number of colours *	16.7 million colours	Power consumption (typical) *	103 W
Display diagonal (metric)	124.46 cm	Power consumption (max)	113 W
High Dynamic Range (HDR) supported	✓	Power consumption (off)	0.3 W
High Dynamic Range (HDR) technology	DisplayHDR 400, High Dynamic Range 10 (HDR10)	AC input voltage	100 - 240 V
Colour gamut standard	DCI-P3	AC input frequency	50 - 60 Hz
Colour gamut	90%	Weight & dimensions	
Performance		Width (with stand)	1215.1 mm
NVIDIA G-SYNC *	✓	Depth (with stand)	281 mm
NVIDIA G-SYNC type	G-SYNC Compatible	Height (with stand)	585.8 mm
AMD FreeSync *	✓	Weight (with stand)	14.7 kg
AMD FreeSync type	FreeSync Premium Pro	Width (without stand)	1215.1 mm
Flicker-free technology	✓	Depth (without stand)	114.2 mm
Low Blue Light technology	✓	Height (without stand)	365.7 mm
Multimedia		Weight (without stand)	12.6 kg
RMS rated power	20 W	Packaging data	
Built-in speaker(s) *	✓	Package width	1330 mm
Built-in camera *	✗	Package depth	490 mm

Design		Packaging data	
Product colour *	Silver	Package height	298 mm
Ports & interfaces		Package weight	19.6 kg
Other features			
Built-in USB hub *	✗	Country of origin	South Korea
USB Power Delivery (USB PD)	✓	Brand specific technologies	Crosshair
USB Power Delivery up to	90 W		
HDMI *	✓		



8806091661203

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.