




Lenovo 4XC7A62582 network card Internal Ethernet 25000 Mbit/s

Brand : Lenovo
Product code: 4XC7A62582
Product name : 4XC7A62582



ThinkSystem Mellanox ConnectX-6 Lx 10/25GbE SFP28 2-Port OCP

Lenovo 4XC7A62582 network card Internal Ethernet 25000 Mbit/s:

The ThinkSystem Mellanox ConnectX-6 Lx 10/25GbE SFP28 Ethernet Adapters are high performance 25Gb Ethernet network adapters that offer multiple network offloads including RoCE v2, NVMe over Ethernet and Open vSwitch.

This product guide provides essential presales information to understand the adapter and its key features, specifications, and compatibility. This guide is intended for technical specialists, sales specialists, sales engineers, IT architects, and other IT professionals who want to learn more about the ConnectX-6 Lx adapters and consider their use in IT solutions.
Lenovo 4XC7A62582. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Maximum data transfer rate: 25000 Mbit/s

Ports & interfaces		Design	
Connectivity technology *	Wired	Internal *	✓
Host interface *	PCI Express	Certification	CB / cTUVus / CE FCC / VCCI / ICES / RCM RoHS
Interface *	Ethernet	Operational conditions	
Fiber ports quantity	2	Operating temperature (T-T)	0 - 55 °C
Fiber optic connector	SFP28	Storage temperature (T-T)	-40 - 70 °C
PCI version	4.0	Operating relative humidity (H-H)	0 - 90%
Network		Weight & dimensions	
Maximum data transfer rate *	25000 Mbit/s	Width	76 mm
Networking standards *	IEEE 802.1Q, IEEE 802.1Qaz, IEEE 802.1Qbb, IEEE 802.1Qbg, IEEE 802.3ad, IEEE 802.3ae, IEEE 802.3ap, IEEE 802.3az, IEEE 802.3by	Depth	115 mm
Design			
Component for *	Server		



0889488542628



889488542628

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.