

Epson WF-C5390DW inkjet printer Colour 4800 x 1200 DPI A4 Wi-Fi

Brand : Epson

Product code: C11CK25401BY

Product name : WF-C5390DW

A4, 4800 x 1200 dpi, 34 pages/min, WiFi, USB, Ethernet, 15.3 kg

Epson WF-C5390DW inkjet printer Colour 4800 x 1200 DPI A4 Wi-Fi:

Reduce your business printing costs and environmental impact, while increasing productivity with less intervention and enhanced security.

- Print speed: 25/25ppm

- Max ink yield: 10k

- Low power consumption

A small workgroup printer perfect for the business environment, from small offices to large corporates. Ideal for those who may have traditionally used lasers and want to cut costs, increase productivity and reduce downtime, while also reducing their environmental impact and improving their CSR reputation.

Epson WF-C5390DW. Colour, Number of print cartridges: 4, Maximum duty cycle: 75000 pages per month. Maximum resolution: 4800 x 1200 DPI. Maximum ISO A-series paper size: A4. Print speed (black, normal quality, A4/US Letter): 34 ppm. Duplex printing. Wi-Fi. Product colour: Black, White



Features		Paper handling	
Recommended duty cycle	250 - 5000 pages per month	Photo paper sizes	10x15,13x18 cm
Duplex printing *	✓	Paper tray media weight	64 - 256 g/m ²
Duplex printing mode	Auto	Ports & interfaces	
Page description languages *	ESC/P-R, PCL 5c, PCL 6, PDF 1.7, PostScript 3	USB port *	✓
Printing colours *	Black, Cyan, Magenta, Yellow	Direct printing	✓
Colour *	✓	Network	
Maximum duty cycle *	75000 pages per month	Ethernet LAN *	✓
Number of print cartridges *	4	Wi-Fi *	✓
Printing		Wi-Fi Direct *	✓
Maximum resolution *	4800 x 1200 DPI	Security algorithms	64-bit WEP, 128-bit WEP, WPA-AES, WPA-PSK, WPA2-AES, WPA2-PSK
Print speed (black, normal quality, A4/US Letter) *	34 ppm	Mobile printing technologies	Apple AirPrint, Epson Email Print, Epson Remote Print, Google Cloud Print
Print speed (colour, normal quality, A4/US Letter)	34 ppm	Performance	
Time to first page (black, normal)	4.8 s	Internal memory *	2057 MB
Time to first page (colour, normal)	5.3 s	Design	
Input & output capacity		Market positioning *	Business
Total number of input trays *	1	Product colour *	Black, White
Total input capacity *	330 sheets	Built-in display *	✓
Total output capacity *	150 sheets	Power	
Maximum input capacity	1830 sheets	Power consumption (printing) *	25 W
Paper handling		Power consumption (off)	0.2 W
Maximum ISO A-series paper size *	A4	Power consumption (ready)	9.8 W
Paper tray media types *	Photo paper, Plain paper	Energy Star Typical Electricity Consumption (TEC)	0.17 kWh/week
ISO A-series sizes (A0...A9) *	A4, A5, A6	AC input voltage	220 - 240 V
Non-ISO print media sizes	Legal, Letter		
Envelopes sizes	10, C4, C5, C6, DL		

Power	
AC input frequency	50 - 60 Hz
Weight & dimensions	
Width	425 mm
Depth	535 mm
Height	357 mm
Weight	15.3 kg



8715946711911

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.