



Lenovo 4XA1L13934 optical disc drive Internal DVD±RW Silver

Brand : Lenovo

Product code: 4XA1L13934

Product name : 4XA1L13934



- Read data in each DVD-ROM, DVD-R (Ver.1.0, Ver. 2.0 for Authoring)
 - Read and writes data in each DVD-R (Ver. 2.1 for General), DVD-R DL (Dual Layer), DVD-RW, DVD-RAM (Ver.2.2), DVD+R, DVD+R DL (Double Layer), and DVD+RW
 - Read data in each CD-ROM, CD-ROM XA, CD-I, Video CD, CD-Extra and CD-Text
 - Read data in Photo CD (Single and Multi session)
 - Read standard CD-DA
 - Read Super Audio CD (Compatible layer in Hybrid type)
 - Read and write CD-R discs conforming to "Orange Book Part 2"
 - Read and write CD-RW discs conforming to "Orange Book Part 3"
 - CPRM (DVD-R/RW/RAM) supported
 - Read and write data on DVD+R (M-DISC)
 - Buffer memory 0.5MB
- ThinkStation Slim 9 mm DVD burner

Lenovo 4XA1L13934 optical disc drive Internal DVD±RW Silver:

ThinkStation Slim 9.0 mm DVD Burner comes with 9.0 mm thickness, perfect fit with ThinkStation Slim Form Factor machines, with fully qualification to assure 100% compatibility on specified machines.

Design		Operational conditions	
Internal *	✓	Storage relative humidity (H-H)	15 - 80%
Product colour	Silver	Weight & dimensions	
Certification	UL, CSA, TUV, SEMKO	Width	128 mm
Performance		Depth	127 mm
Purpose *	Desktop	Height	9 mm
Optical drive type *	DVD±RW	Weight	160 g
Interface *	Serial ATA	Packaging data	
Disc types supported	CD-DA, CD-R, CD-ROM, CD-RW, DVD+R, DVD+R DL, DVD+RW, DVD-R, DVD-R DL, DVD-RAM, DVD-ROM, DVD-RW	Package width	190 mm
		Package depth	180 mm
		Package height	105 mm
		Package weight	454 g
Drive device, buffer size	0.5 MB	Packaging content	
Compatible products	P340/P350/P360 TWR	Quantity per pack	1 pc(s)
Operational conditions		Warranty card	✓
Operating relative humidity (H-H)	15 - 85%		
Operating temperature (T-T)	5 - 50 °C		
Storage temperature (T-T)	5 - 45 °C		



0195892080855



195892080855

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.