

ASUS ProArt PA248CRV computer monitor 61.2 cm (24.1") 1920 x 1200 pixels WUXGA LCD Black, Silver

Brand : ASUS

Product family: ProArt

Product code: 90LM05K0-B01K70

Product name : PA248CRV

- 24.1-inch 16:10 WUXGA (1920 x 1200) LED backlight HDR display with 178° wide-view IPS panel
 - Wide color gamut with 97% DCI-P3 and 100% sRGB coverage
 - Calman Verified and factory pre-calibrated to Delta E < 2 color accuracy
 - Extensive connectivity, including DisplayPort™ over USB-C® with 96-watt Power Delivery, DisplayPort™, HDMI®, and USB hub
 - Slim profile and compact base, plus wall-mountable design to maximize desk space
 - Ergonomic design with tilt, swivel, pivot, and height adjustments for comfortable viewing
 - Green sustainability with paper packaging and energy-efficient performance that meets environmental standards
- ASUS ProArt Display PA248CRV Professional Monitor – 24.1-inch, IPS, 16:10, WUXGA (1920 x 1200), 97% DCI-P3, Color Accuracy ΔE < 2, Calman Verified, HDR-10, USB-C PD 96W, VESA MediaSync, Ergonomic Stand, Green Sustainability



Display		Ports & interfaces	
Display diagonal *	61.2 cm (24.1")	HDMI *	✓
Display resolution *	1920 x 1200 pixels	HDMI ports quantity	2
HD type *	WUXGA	HDMI version	1.4
Native aspect ratio *	16:10	DisplayPorts quantity	2
Display technology *	LCD	DisplayPort version	1.4
Panel type *	IPS	Headphone out *	✓
Backlight type	LED	Headphone outputs	1
Touchscreen *	✗	HDCP	✓
Display brightness (typical)	350 cd/m²	HDCP version	1.4
Response time *	5 ms	Charging port type	USB Type-C
Anti-glare screen	✓	Ergonomics	
Screen shape *	Flat	VESA mounting *	✓
Contrast ratio (typical) *	1000:1	Panel mounting interface	100 x 100 mm
Maximum refresh rate *	75 Hz	Wall mountable	✓
Viewing angle, horizontal	178°	Cable lock slot *	✓
Viewing angle, vertical	178°	Cable lock slot type	Kensington
Display number of colours *	16.7 million colours	Height adjustment *	✓
Pixel pitch	0.27 x 0.27 mm	Adjustable height (max)	13 cm
Pixel density	94 ppi	Pivot	✓
Viewable size, horizontal	51.8 cm	Pivot angle	-90 - 90°
Viewable size, vertical	32.4 cm	Swivelling	✓
Digital horizontal frequency	95 - 95 kHz	Swivel angle range	-30 - 30°
Digital vertical frequency	48 - 75 Hz	Tilt adjustment	✓
High Dynamic Range (HDR) supported	✓	Tilt angle range	-5 - 23°
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10)	Power	
Colour gamut standard	DCI-P3	Energy efficiency class (SDR) *	D
Colour gamut	97%	Energy efficiency class (HDR) *	E

Display		Power	
sRGB coverage (typical)	100%	Energy consumption (SDR) per 1000 hours *	15 kWh
Performance		Energy consumption (HDR) per 1000 hours *	18 kWh
VESA Adaptive Sync support	✓	Power consumption (typical) *	12.35 W
Flicker-free technology	✓	Power consumption (off)	0 W
Low Blue Light technology	✓	Power consumption (PowerSave)	0.5 W
Multimedia		AC input voltage	100 - 240 V
Number of speakers	2	AC input frequency	50 - 60 Hz
RMS rated power	4 W	Energy efficiency scale	A to G
Built-in speaker(s) *	✓	Weight & dimensions	
Built-in camera *	✗	Width (with stand)	531.7 mm
Design		Depth (with stand)	190.4 mm
Market positioning *	Graphics design	Height (with stand)	529.2 mm
Product colour *	Black, Silver	Weight (with stand)	5.9 kg
Feet colour	Silver	Width (without stand)	531.7 mm
Ports & interfaces		Depth (without stand)	44.1 mm
Built-in USB hub *	✓	Height (without stand)	350.2 mm
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Weight (without stand)	4.2 kg
USB upstream port type	USB Type-C	Packaging data	
USB Type-A downstream ports quantity	3	Package width	610 mm
USB Type-C downstream ports quantity	1	Package depth	126 mm
USB Type-C DisplayPort Alternate Mode	✓	Package height	414 mm
USB Power Delivery (USB PD)	✓	Package weight	8.5 kg
USB Power Delivery up to	96 W	Package type	Box



4711081951490



0195553977258



195553977258



0195553951494



195553951494

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.