

ASUS PRIME B650-PLUS AMD B650 Socket AM5 ATX

Brand : ASUS

Product code: 90MB1BS0-M0EAY0

Product name : PRIME B650-PLUS

- AMD AM5 Socket: Ready for AMD Ryzen™ 7000 Series Desktop Processors
 - Ultrafast Connectivity: M.2 PCIe 5.0, Realtek 2.5Gb Ethernet, USB 3.2 Gen 2 Type-C®, front USB 3.2 Gen 1 Type-C®, USB4® Support
 - ASUS OptiMem II: Careful routing of traces and vias, plus ground layer optimizations to preserve signal integrity for improved memory overclocking
 - Comprehensive Cooling: VRM heatsink, M.2 heatsink, PCH heatsink, hybrid fan headers and Fan Xpert 2+
 - Aura Sync RGB Lighting: Onboard Addressable Gen 2 headers and Aura RGB header for RGB LED strips, easily synced with Aura Sync-capable hardware
- AMD B650 ATX motherboard with DDR5, PCIe 5.0 M.2 support, Realtek 2.5Gb Ethernet, DisplayPort, HDMI®, SATA 6 Gbps, USB 3.2 Gen 2 Type-C®, front USB 3.2 Gen 1 Type-C®, BIOS FlashBack™, USB4® Support and Arua Sync support



Processor		Rear panel I/O ports	
Processor manufacturer *	AMD	USB 3.2 Gen 2 (3.1 Gen 2) Type-A ports quantity *	3
Processor socket *	Socket AM5	USB 3.2 Gen 2 (3.1 Gen 2) Type-C ports quantity *	1
Compatible processor series *	AMD Ryzen 7000 Series	Ethernet LAN (RJ-45) ports *	1
Supported processor sockets	Socket AM5	HDMI ports quantity *	1
Memory		HDMI version	2.1
Supported memory types *	DDR5-SDRAM	DisplayPorts quantity	1
Number of memory slots *	4	DisplayPort version	1.4
Memory slots type	DIMM	Headphone outputs	1
Memory channels	Dual-channel	Line-in	✓
ECC compatibility	ECC & Non-ECC	Microphone in	✓
Supported memory clock speeds	4800,5000,5200,5400,5600,5800,6000,6200,6400 MHz	S/PDIF out port	✓
Supported memory clock speed (max)	6400 MHz	Network	
Maximum internal memory *	128 GB	Ethernet LAN	✓
Unbuffered memory	✓	Ethernet interface type	2.5 Gigabit Ethernet
Storage controllers		Wi-Fi *	✗
Supported storage drive types	HDD & SSD	Features	
Supported storage drive interfaces *	M.2, SATA III	Motherboard chipset *	AMD B650
RAID support	✓	Audio output channels *	7.1 channels
RAID levels	0, 1, 10	Product colour	Multicolour
Graphics		Component for *	PC
Parallel processing technology support *	Not supported	Motherboard form factor *	ATX
On-board graphics card	✗	Motherboard chipset family *	AMD
Internal I/O		Power source type	ATX
USB 2.0 connectors *	2	Windows operating systems supported	Windows 10, Windows 11 x64
USB 3.2 Gen 1 (3.1 Gen 1) connectors *	2		
Number of SATA III connectors *	4		

Internal I/O		Expansion slots	
Front panel audio connector	✓	PCI Express x4 (Gen 1.x) slots	2
ATX Power connector (24-pin)	✓	PCI Express x16 (Gen 4.x) slots	2
CPU fan connector	✓	Number of M.2 (M) slots	2
Number of chassis fan connectors	3	BIOS	
EPS power connector (8-pin)	✓	BIOS type *	UEFI AMI
Number of COM connectors	1	BIOS memory size	256 Mbit
TPM connector	✓	Packaging data	
Thunderbolt headers	1	Package width	338 mm
12V power connector	✓	Package depth	373 mm
RGB LED pin header	✓	Package height	68 mm
Rear panel I/O ports		Package weight	1.35 kg
USB 2.0 ports quantity *	2	Weight & dimensions	
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity *	2	Width	305 mm
		Depth	244 mm
		Packaging content	
		Cables included	SATA
		User guide	✓
		Other features	
		Back-to-BIOS button	✓
		Number of M.2 (E) slots	1




4711081923381



0195553923385



195553923385



4711081923398

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.