

ASUS ZenBeam E1R Standard throw projector 200 ANSI lumens LED WVGA (854x480) Silver



Brand : ASUS

Product code: 90LJ00J3-B01070

Product name : ZenBeam E1R

- Automatic portrait projection mode* makes it ideal for viewing social media content
- Enables up to 100-inch projections at 2.7m and includes auto vertical keystone correction and tripod socket for convenience
- Light source of 200 LED lumens with native WVGA (854 x 480) resolution and also supports FHD content

- Built-in battery: Enables up to four hours* of video playback

ZenBeam E1R mini LED projector – 200 LED lumens, WVGA (854x480) resolution, automatic portrait projection mode, built-in battery for up to 4-hour portable video playback , power bank, USB Type-A, HDMI

ASUS ZenBeam E1R. Projector brightness: 200 ANSI lumens, Projection technology: LED, Projector native resolution: WVGA (854x480). Light source type: LED, Service life of light source: 30000 h. Focus: Manual, Zoom ratio: Fixed, Throw ratio: 1.2:1. HDMI connector type: Full-size. Noise level: 30 dB, Noise level (economic mode): 28 dB

Projector		Features	
Screen size compatibility *	406.4 - 3048 mm (16 - 120")	Noise level *	30 dB
Projection distance	0.5 - 3.7 m	Multimedia	
Projector brightness *	200 ANSI lumens	Built-in speaker(s) *	✓
Projection technology *	LED	RMS rated power	2 W
Projector native resolution *	WVGA (854x480)	Number of built-in speakers	1
Contrast ratio (typical) *	500:1	Design	
Native aspect ratio *	16:9	Market positioning *	Portable
Number of colours	16.7 million colours	Product type *	Standard throw projector
Colour gamut	120%	Product colour *	Silver
Light source		Placement	Ceiling, Desktop
Light source type *	LED	Display	
Service life of light source *	30000 h	Built-in display *	✗
Lens system		Power	
Focus *	Manual	Power source *	DC
Zoom ratio	Fixed	Power consumption (typical) *	45 W
Throw ratio	1.2:1	Power consumption (standby) *	0.5 W
Offset	100%	Power consumption (max)	45 W
Video		Battery capacity	5700 mAh
Analog signal format system *	Not supported	Battery life (max)	4 h
Full HD *	✓	Operational conditions	
3D *	✗	Operating temperature (T-T)	0 - 40 °C
Ports & interfaces		Operating relative humidity (H-H)	20 - 90%
HDMI connector type	Full-size	Weight & dimensions	
USB 2.0 ports quantity	1	Width	84 mm
Headphone outputs	1	Depth	108 mm
HDMI ports quantity *	1	Height	29 mm
DVI port *	✗	Weight *	310 g
DC-in jack	✓	Package width	210 mm
Network		Package depth	135 mm
Smart TV *	✗	Package height	100.5 mm
Ethernet LAN *	✗	Package weight	1.05 kg

Storage		Packaging content	
Card reader integrated *	✗	Remote control included *	✗
Features		Cables included	AC, HDMI, USB Type-C
Noise level (economic mode)	28 dB	AC adapter included	✓
HDCP	✓	Warranty card	✓



4711081642305

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.