

ASUS ZenScreen MB249C computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD LED Black

Brand : ASUS

Product family: ZenScreen

Product code: 90LM0865-B01170

Product name : MB249C

- Frameless 23.8-inch FHD IPS display with anti-glare surface coating for seamless multi-monitor setups and improved viewing experiences
 - Sleek, ultraslim profile and 2.8 kg overall weight enable effortless portability
 - Multiple stand options and accessories, including an integrated carrying handle/kickstand, height-adjustable C-clamp with Z-axis adjustment, and partition hook kit for flexible placement
 - Rich connectivity options include a full-function USB-C® with 60-watt power delivery, HDMI®, and earphone jack
 - Environmentally friendly design with ENERGY STAR®-certified energy efficiency, and packaged in FSC® certified paper
- ZenScreen MB249C portable 24 inch monitor (Full HD, IPS, USB-C, HDMI, speakers, carrying handle, kickstand, C-clamp)



Display		Ports & interfaces	
Display diagonal *	60.5 cm (23.8")	HDCP	✓
Display resolution *	1920 x 1080 pixels	HDCP version	1.4
HD type *	Full HD	Charging port type	USB Type-C
Native aspect ratio *	16:9	DC-in jack	✓
Display technology *	LED	Ergonomics	
Panel type *	IPS	VESA mounting *	✓
Backlight type	LED	Panel mounting interface	100 x 100 mm
Touchscreen *	✗	Wall mountable	✓
Display brightness (typical)	250 cd/m²	Cable lock slot *	✓
Response time *	5 ms	Cable lock slot type	Kensington
Anti-glare screen	✓	Height adjustment *	✓
Screen shape *	Flat	Adjustable height (max)	18 cm
Contrast ratio (typical) *	1000:1	Pivot	✓
Maximum refresh rate *	75 Hz	Pivot angle	0 - 90°
Viewing angle, horizontal	178°	Swivelling	✓
Viewing angle, vertical	178°	Swivel angle range	-90 - 90°
Display number of colours *	16.7 million colours	Tilt adjustment	✓
Pixel pitch	0.2745 x 0.2745 mm	Tilt angle range	-5 - 20°
Viewable size, horizontal	52.7 cm	Power	
Viewable size, vertical	29.6 cm	Energy efficiency class (SDR) *	D
Digital horizontal frequency	24 - 84 kHz	Energy efficiency class (HDR) *	Not available
Digital vertical frequency	48 - 75 Hz	Energy consumption (SDR) per 1000 hours *	14 kWh
Performance		Power consumption (typical) *	13 W
NVIDIA G-SYNC *	✗	Power consumption (standby) *	0.3 W
AMD FreeSync *	✓	Power consumption (off)	0.3 W
AMD FreeSync type	FreeSync	Power consumption (PowerSave)	0.5 W
Flicker-free technology	✓		
Low Blue Light technology	✓		

Performance		Power	
Game mode	✓	AC input voltage	100 - 240 V
Multimedia		AC input frequency	50 - 60 Hz
Number of speakers	2	Power supply type	External
RMS rated power	2 W	Weight & dimensions	
Built-in speaker(s) *	✓	Width (with stand)	539.3 mm
Built-in camera *	✗	Depth (with stand)	302.2 mm
Design		Height (with stand)	711.4 mm
Market positioning *	Home	Weight (with stand)	4.84 kg
Product colour *	Black	Width (without stand)	539.3 mm
Ports & interfaces		Depth (without stand)	23.6 mm
Built-in USB hub *	✓	Height (without stand)	346.3 mm
USB upstream port type	USB Type-C	Weight (without stand)	2.85 kg
Number of upstream ports	1	Packaging data	
Number of USB Type-C upstream ports quantity	1	Package width	600 mm
USB Type-C DisplayPort Alternate Mode	✓	Package depth	124 mm
USB Power Delivery (USB PD)	✓	Package height	426 mm
USB Power Delivery up to	60 W	Package weight	7.6 kg
HDMI *	✓	Package type	Box
HDMI ports quantity	1	Packaging content	
HDMI version	1.4	Cables included	AC, HDMI, USB Type-C
Headphone out *	✓	Power adapter included	✓



4711081911432



0195553963664



195553963664



5715328145948

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.