

StarTech.com RUSB2CLTMM1MR mobile phone cable Black 1 m
USB C Lightning

Brand : StarTech.com

Product code: RUSB2CLTMM1MR

Product name : RUSB2CLTMM1MR

StarTech.com 3ft (1m) Durable USB-C to Lightning Cable - Right-Angled Heavy Duty Aramid Fiber USB Type-C to Lightning Charging/Sync Cord - Apple MFi Certified - Rugged iPhone Lightning Cable
StarTech.com RUSB2CLTMM1MR. Cable length: 1 m, Connector 1: USB C, Connector 2: Lightning.
Package width: 128 mm, Package depth: 220 mm, Package height: 30 mm. Master (outer) case width: 380 mm, Master (outer) case length: 430 mm, Master (outer) case height: 290 mm



Features		Features	
Product colour *	Black	Plug and Play	✓
Cable length *	1 m	Weight	23 g
Connector 1 *	USB C	Technical details	
Connector 2 *	Lightning	Sustainability compliance	✓
Connector 1 gender	Male	Compliance certificates	RoHS
Connector 2 gender	Male	Packaging data	
Connector 1 form factor	Straight	Package width	128 mm
Connector 2 form factor	Angled	Package depth	220 mm
USB version	USB 2.0	Package height	30 mm
Maximum data transfer rate	480 Mbit/s	Package weight	25.8 g
Connector contacts plating	Nickel/Gold	Logistics data	
Jacket material	Thermoplastic elastomer (TPE)	Master (outer) case width	380 mm
Cable shielding	Aluminum mylar foil	Master (outer) case length	430 mm
AWG wire size	32/22	Master (outer) case height	290 mm
Output current (max)	3 A	Products per master (outer) case	300 pc(s)



0065030893794



065030893794

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.