

ASUS BR1100F-CDXA-3Y Intel® Celeron® N N4500 Hybrid (2-in-1) 29.5 cm (11.6") Touchscreen HD 4 GB DDR4-SDRAM 128 GB eMMC Wi-Fi 6 (802.11ax) Windows 11 Pro Academic Grey

Brand : ASUS

Product code: 90NX03A1-M00YP0

Product name : BR1100F-CDXA-3Y

- Windows 11 Pro Education
- 4 GB memory
- 128 GB eMMC
- Ruggedized Design
- Dual-band WiFi 6 (802.11ax)
- AI Noise Canceling
- TÜV Rheinland certified display

Intel Celeron N4500 (4MB Cache, 1.1GHz), 4GB DDR4-SDRAM, 128GB eMMC, 29.5 cm (11.6") HD 1366 x 768 Touch, Intel UHD Graphics, LAN, WLAN, Webcam, Windows 11 Pro Academic 64-bit
ASUS BR1100F-CDXA-3Y. Product type: Hybrid (2-in-1), Form factor: Convertible (Folder). Processor family: Intel® Celeron® N, Processor model: N4500, Processor frequency: 1.1 GHz. Display diagonal: 29.5 cm (11.6"), HD type: HD, Display resolution: 1366 x 768 pixels, Touchscreen. Internal memory: 4 GB, Internal memory type: DDR4-SDRAM. Total storage capacity: 128 GB, Storage media: eMMC. Operating system installed: Windows 11 Pro Academic. Product colour: Grey



Design		Network	
Colour name	Dark Grey	Wi-Fi standards	Wi-Fi 6 (802.11ax)
Product type *	Hybrid (2-in-1)	Mobile network connection *	✗
Product colour *	Grey	Antenna type	2x2
Form factor *	Convertible (Folder)	Ethernet LAN	✓
Housing material	Plastic	Ethernet LAN data rates	10,100,1000 Mbit/s
Display		Bluetooth	✓
Display diagonal *	29.5 cm (11.6")	Bluetooth version	5.3
Display resolution *	1366 x 768 pixels	Ports & interfaces	
Touchscreen *	✓	USB 2.0 ports quantity *	1
HD type	HD	USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity *	1
LED backlight	✓	USB 3.2 Gen 2 (3.1 Gen 2) Type-C ports quantity	1
Native aspect ratio	16:9	Ethernet LAN (RJ-45) ports	1
Display surface	Gloss	HDMI ports quantity *	1
Display brightness	200 cd/m²	HDMI version	1.4
RGB colour space	NTSC	Combo headphone/mic port	✓
Colour gamut	50%	Keyboard	
Processor		Pointing device	Touchpad
Processor manufacturer *	Intel	Numeric keypad *	✗
Processor family *	Intel® Celeron® N	Software	
Processor model *	N4500	Operating system architecture	64-bit
Processor cores	2	Trial software	1-month trial for new Microsoft 365 customers
Processor boost frequency	2.8 GHz	Operating system installed *	Windows 11 Pro Academic
Processor frequency *	1.1 GHz	Processor special features	
Processor cache	4 MB	CPU configuration (max)	1
Processor cache type	Smart Cache		
Memory			
Internal memory *	4 GB		

Memory		Battery	
Internal memory type	DDR4-SDRAM	Battery technology	Lithium-Ion (Li-Ion)
Memory form factor	On-board	Number of battery cells	3
Maximum internal memory *	4 GB	Battery capacity *	42 Wh
Storage		Power	
Total storage capacity *	128 GB	AC adapter power	45 W
Storage media *	eMMC	AC adapter frequency	50 - 60 Hz
Optical drive type *	✗	AC adapter input voltage	100 - 240 V
Graphics		AC adapter output current	2.37 A
Discrete graphics card model *	Not available	AC adapter output voltage	19 V
On-board graphics card *	✓	DC-in jack	✓
On-board GPU manufacturer	Intel	USB Type-C charging port *	✓
Discrete graphics card *	✗	USB Power Delivery (USB PD)	✓
On-board graphics card model *	Intel® UHD Graphics	Security	
Audio		Cable lock slot	✓
Audio system	SonicMaster	Cable lock slot type	Kensington
Built-in microphone	✓	Trusted Platform Module (TPM)	✓
Camera		Weight & dimensions	
Front camera	✓	Width	294.6 mm
Front camera HD type	HD	Depth	204.9 mm
Privacy camera	✓	Height (front)	1.99 cm
Privacy type	Privacy shutter	Height (rear)	2 cm
Rear camera	✓	Weight *	1.4 kg
Rear camera resolution (numeric)	13 MP	Packaging content	
Network		AC adapter included *	✓
Top Wi-Fi standard *	Wi-Fi 6 (802.11ax)		



4711387086421



0197105086425



197105086425

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.