



BenQ LU960 Standard throw projector 5500 ANSI lumens DLP WUXGA (1920x1200) 3D Black

Brand : BenQ

Product code: 9H.JN477.25E

Product name : LU960

- Dustproofing technology for long-lasting performance
- Support lens shift with Lens Lock
- < 16.67 ms low latency enables realistic simulation
- White balance calibration for seamless blending
- Support 360° and portrait installation

DLP, WUXGA, 1920 x 1200, 5500 ANSI, 10W, HDMI, USB, RS232, RJ45, 479.6 x 182.8 x 402 mm, 12 kg
BenQ LU960. Projector brightness: 5500 ANSI lumens, Projection technology: DLP, Projector native resolution: WUXGA (1920x1200). Light source type: Laser, Service life of light source: 20000 h, Service life of light source (economic mode): 38000 h. Zoom ratio: 1.1:1, Throw ratio: 1.127 - 1.697. Analog signal format system: NTSC, PAL, SECAM, Supported graphics resolutions: 640 x 512, 640 x 640, 640 x 160, 640 x 352, 640 x 360, 640 x 400, 640 x 480 (VGA), 640 x 544, 640..., Supported video modes: 480i, 480p, 576i, 576p, 720p, 1080i, 1080p. Serial interface type: RS-232



Projector		Network	
Screen size compatibility *	762 - 7620 mm (30 - 300")	Ethernet LAN (RJ-45) ports	1
Projector brightness *	5500 ANSI lumens	Features	
Projection technology *	DLP	Noise level (economic mode)	35 dB
Projector native resolution *	WUXGA (1920x1200)	On Screen Display (OSD)	✓
Contrast ratio (typical) *	3000000:1	On Screen Display (OSD) languages	Arabic, Bulgarian, Simplified Chinese, Traditional Chinese, Croatian, Czech, Danish, German, Dutch, English, Spanish, Finnish, French, Greek, Hindi, Hungarian, Indonesian, Italian, Japanese, Korean, Norwegian, Polish, Portuguese, Romanian, Russian, Swedish, Thai, Turkish
Native aspect ratio *	16:9		
Number of colours	1.07 billion colours	Number of OSD languages	28
Horizontal scan range	15 - 135 kHz	Noise level *	37 dB
Vertical scan range	23 - 120 Hz	Multimedia	
Keystone correction, horizontal	-40 - 40°	Built-in speaker(s) *	✓
Keystone correction, vertical	-30 - 30°	RMS rated power	10 W
Light source		Design	
Light source type *	Laser	Market positioning *	Business
Service life of light source *	20000 h	Product type *	Standard throw projector
Service life of light source (economic mode)	38000 h	Product colour *	Black
Lens system		Cable lock slot	✓
Zoom capability	✓	Cable lock slot type	Kensington
Zoom ratio	1.1:1	Power	
Throw ratio	1.127 - 1.697	Power source *	AC
Offset	0%	Power consumption (typical) *	450 W
Video		Power consumption (standby) *	0.5 W
Analog signal format system *	NTSC, PAL, SECAM	Power consumption (max)	500 W
Full HD *	✓		
3D *	✓		

Video		Power	
Supported graphics resolutions	640 x 512, 640 x 640, 640 x 160, 640 x 352, 640 x 360, 640 x 400, 640 x 480 (VGA), 640 x 544, 640 x 576, 640 x 960, 704 x 480, 704 x 576, 720 x 350, 720 x 400, 720 x 480, 720 x 576, 720 x 720, 752 x 582, 768 x 432, 768 x 448, 768 x 494, 768 x 576, 800 x 448, 800 x 450, 800 x 480 (WVGA), 800 x 500, 800 x 592, 800 x 600 (SVGA), 832 x 624, 832 x 642, 848 x 480, 854 x 480 (WVGA), 900 x 720, 960 x 960, 960 x 480, 960 x 540, 960 x 576, 960 x 720, 1024 x 576 (WSVGA), 1024 x 600, 1024 x 640, 1024 x 768 (XGA), 1024 x 800, 1032 x 452, 1056 x 144, 1080 x 1080, 1152 x 864 (XGA+), 1152 x 870, 1200 x 1600, 1200 x 1920, 1280 x 1024 (SXGA), 1280 x 720 (HD 720), 1280 x 768 (WXGA), 1280 x 768, 1280 x 800 (WXGA), 1280 x 800, 1280 x 960, 1280 x 1280, 1284 x 560, 1296 x 732, 1360 x 768 (WXGA), 1366 x 480, 1366 x 760, 1366 x 768, 1366 x 768, 1368 x 768, 1376 x 768, 1400 x 1050 (SXGA+), 1400 x 1080, 1400 x 900, 1440 x 1050, 1440 x 1080, 1440 x 234, 1440 x 900 (WXGA+), 1440 x 900, 1440 x 912, 1536 X 6144, 1536 x 2048, 1536 x 1536, 1600 x 1200 (UXGA), 1600 x 1280, 1600 x 600, 1600 x 900, 1600 x 904, 1680 x 1050 (WSXGA+), 1680 x 1056, 1920 x 1080 (HD 1080), 1920 x 1200 (WUXGA), 1920 x 1440, 1920 x 1600, 1920 x 2160, 1920 x 480, 1920 x 502, 1920 x 1920, 1920 x 720, 1920 x 832, 2032 x 1920, 2048 x 1080, 2048 x 1152, 2048 x 1280, 2048 x 1520, 2048 x 1536 (QXGA), 2048 x 1640, 2048 x 2560, 2048 x 2048, 2192 x 2192, 2304 x 1296, 2304 x 1728, 2520 x 1520, 2550 x 1440, 2560 x 1080, 2560 x 1440, 2560 x 1600 (WQXGA), 2560 x 1656, 2560 x 1920, 2560 x 1944, 2560 x 2048, 2592 x 1520, 2592 x 1944, 2640 x 2640, 2688 x 1512, 2688 x 1520, 2800 x 2100, 2880 x 1264, 2880 x 1620, 2880 x 2880, 2880 x 2160, 2944 x 1656, 2992 x 2244, 3072 x 1728, 3072 x 2048, 3200 x 1800, 3264 x 2448, 3280 x 2048, 3440 x 1440, 3648 x 2736, 3840 x 1200, 3840 x 2160	Power consumption (economy mode)	350 W
		AC input voltage	100 - 240 V
		Operational conditions	
		Operating temperature (T-T)	0 - 40 °C
		Weight & dimensions	
		Width	479.6 mm
		Depth	402 mm
		Height	182.8 mm
		Weight *	12 kg
		Packaging content	
		Remote control included *	✓
		Batteries included	✓
	Cables included	AC	
	Packaging content	Installation Guide Safety Guide Remote Control (RCA024) AA Batteryx2 Power Cord Warranty card (by Region)	
	Other features		
	Security updates end date	31/12/2024	
Supported video modes	480i, 480p, 576i, 576p, 720p, 1080i, 1080p		
Ports & interfaces			
USB 2.0 ports quantity	1		
Mini-USB 2.0 ports quantity	1		
Audio (L/R) in *	1		
Audio (L/R) out	1		
Serial interface type *	RS-232		
PC in (D-Sub)	✓		
HDMI ports quantity *	2		
Network			
Ethernet LAN *	✓		



4718755084010

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.