

StarTech.com SV231DPUCA KVM switch Black

Brand : StarTech.com

Product code: SV231DPUCA

Product name : SV231DPUCA

StarTech.com 2-Port USB-C KVM Switch, Single 4K 60Hz DisplayPort Monitor, 3.5mm Audio, 6x USB Hub Ports, Hot Key Switching, Thunderbolt 3/4 Compatible - TAA

StarTech.com SV231DPUCA. Keyboard port type: USB, Mouse port type: USB, Video port type:

DisplayPort. HD type: 4K Ultra HD, Maximum resolution: 5120 x 1440 pixels, Video bandwidth: 60 Hz.

Product colour: Black, Mean time between failures (MTBF): 158000 h. Power source: AC, Input voltage:

100 - 240 V, Input current: 1.2 A. Width: 140 mm, Depth: 160 mm, Height: 40 mm



Ports & interfaces		Display	
Number of computers controlled *	2	Built-in display *	✗
Keyboard port type *	USB	Power	
Mouse port type *	USB	Power source	AC
Video port type *	DisplayPort	Input voltage	100 - 240 V
DisplayPort version	1.2	Input current	1.2 A
Console ports *	3.5mm headphone, 3.5mm mic, DisplayPort	Output voltage	12 V
Console USB ports quantity	6	Output current	3 A
Console DisplayPorts ports quantity	1	Power plug type	Type M
USB hub	✓	Operational conditions	
USB 3.2 Gen 1 (3.1 Gen 1) Type-A hub ports quantity	2	Operating temperature (T-T)	0 - 40 °C
Headphone outputs	1	Storage temperature (T-T)	-10 - 60 °C
Number of microphone inputs	1	Operating relative humidity (H-H)	0 - 80%
Performance		Weight & dimensions	
HD type *	4K Ultra HD	Width	140 mm
Maximum resolution *	5120 x 1440 pixels	Depth	160 mm
Video bandwidth	60 Hz	Height	40 mm
Data transfer rate (max)	5 Gbit/s	Weight	600 g
Scan interval	3,8,15,30 s	Packaging data	
HDCP	✓	Package width	184 mm
Chipset	Parade - PS8461, Etron - EJ899I	Package depth	238 mm
Audio channels	2.0	Package height	89 mm
Number of displays supported	1	Package weight	1 kg
Design		Packaging content	
Rack mounting *	✗	Quick installation guide	✓
Product colour *	Black	AC adapter included	✓
LED indicators	✓	Rubber feet	✓

Design		Other features	
Push button	✓	IP control	✗
Hot keys	✓	Logistics data	
Mean time between failures (MTBF)	158000 h	Master (outer) case width	300 mm
		Master (outer) case length	397 mm
		Master (outer) case height	257 mm
		Products per master (outer) case	6 pc(s)



0065030872201



065030872201

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.