

TP-Link Bluetooth 5.0 Nano USB Adapter

Brand : TP-Link

Product code: UB500

Product name : Bluetooth 5.0 Nano USB Adapter

- Bluetooth 5.0 – Applies the latest Bluetooth 5.0 technology, backward compatible with Bluetooth V4.0/3.0/2.1/2.0/1.1
 - Wireless Connectivity – Provides stable and convenient communication between Bluetooth devices and your PC or laptop
 - Nano-Sized – Ultra-small for convenient portability with reliable high performance
 - Supported Operating System – Windows 10/8.1/7
- Bluetooth 5.0, USB 2.0, 14.8 × 6.8 × 18.9 mm
 TP-Link Bluetooth 5.0 Nano USB Adapter. Connectivity technology: Wireless, Host interface: USB Type-A, Interface: Bluetooth. USB powered. Product colour: Black



Ports & interfaces		Operational conditions	
Connectivity technology *	Wireless	Operating relative humidity (H-H)	10 - 90%
Host interface *	USB Type-A	Storage relative humidity (H-H)	5 - 90%
Interface *	Bluetooth	Sustainability	
USB version	2.0	Sustainability compliance	✓
Network		Weight & dimensions	
Bluetooth	✓	Width	14.8 mm
Bluetooth version	5.0	Depth	6.8 mm
		Height	18.9 mm
Design		Packaging data	
Component for *	PC/Laptop	Package width	118 mm
Product colour	Black	Package depth	102 mm
Internal *	✗	Package height	23 mm
		Package weight	30 g
Power		Packaging content	
USB powered	✓	Quick installation guide	✓
		Technical details	
		Compliance certificates	CE, Federal Communications Commission (FCC)
		Logistics data	
		Harmonized System (HS) code	84733020

System requirements	
Windows operating systems supported	Windows 10, Windows 10 Education, Windows 10 Education x64, Windows 10 Enterprise, Windows 10 Enterprise x64, Windows 10 Home, Windows 10 Home x64, Windows 10 IOT Core, Windows 10 IoT Enterprise, Windows 10 Pro, Windows 10 Pro x64, Windows 10 x64, Windows 7, Windows 7 Enterprise, Windows 7 Enterprise x64, Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 7 x64, Windows 8.1, Windows 8.1 Enterprise, Windows 8.1 Enterprise x64, Windows 8.1 Pro, Windows 8.1 Pro x64, Windows 8.1 x64


Operational conditions	
Operating temperature (T-T)	0 - 40 °C



4897098683439



4897098683446



0840030703447



840030703447

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.