

ASUS MB16ACV computer monitor 39.6 cm (15.6") 1920 x 1080 pixels Full HD LED Black

Brand : ASUS

Product code: 90LM0381-B01370

Product name : MB16ACV

- 15.6-inch Full HD portable anti-glare IPS display with an ultraslim and thin design helps you get things done more efficiently when you're on the go
 - Kickstand design prop the monitor up in either portrait or landscape mode easily
 - Features a hybrid-signal solution that supports power and video transmission, and enables compatibility with any laptop with a USB Type-C or Type A port
 - ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience
 - Proprietary long-lasting antibacterial treatment inhibits the growth of bacteria and fungi on the monitor
- ZenScreen MB16ACV Portable USB Monitor- 15.6 inch Full HD, IPS, Hybrid Signal Solution, USB Type-C, Flicker Free, Blue Light Filter, Anti-glare surface, Antibacterial treatment



Display		Network	
Display diagonal *	39.6 cm (15.6")	Wi-Fi	×
Display resolution *	1920 x 1080 pixels	Ergonomics	
HD type *	Full HD	VESA mounting *	×
Native aspect ratio *	16:9	Cable lock slot *	×
Display technology *	LED	Height adjustment *	×
Panel type *	IPS	Power	
Touchscreen *	×	Energy efficiency class (SDR) *	F
Response time *	5 ms	Energy consumption (SDR) per 1000 hours *	13 kWh
Screen shape *	Flat	Power consumption (typical) *	15 W
Contrast ratio (typical) *	800:1	Power consumption (off)	0.3 W
Maximum refresh rate *	60 Hz	AC input voltage	100 - 240 V
Performance		AC input frequency	50 - 60 Hz
NVIDIA G-SYNC *	×	Energy efficiency scale	A to G
AMD FreeSync *	×	Weight & dimensions	
Multimedia		Width (with stand)	357.9 mm
Built-in speaker(s) *	×	Depth (with stand)	10.5 mm
Built-in camera *	×	Height (with stand)	224.8 mm
Design		Weight (with stand)	830 g
Product colour *	Black	Packaging data	
Ports & interfaces		Package width	433 mm
USB Type-C DisplayPort Alternate Mode	✓	Package depth	82 mm
HDMI *	×	Package height	283 mm
Headphone out *	×	Package weight	2.7 kg
HDCP	✓	Logistics data	
		Harmonized System (HS) code	85285210



4718017949040



0192876978498



192876978498



4718017978477

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.