



TP-Link AX1800 wireless router Gigabit Ethernet Dual-band (2.4 GHz / 5 GHz) White

Brand : TP-Link

Product code: EX230V

Product name : AX1800

- AX1800 Dual-Band Wi-Fi 6: 1201 Mbps (5 GHz) + 574 Mbps (2.4 GHz).*
- 802.11ax Technology: Create a seamless Wi-Fi network in your home with the revolutionary combination of OFDMA, MU-MIMO, and Beamforming technologies.**
- Ultra Connectivity: 1x Gigabit WAN + 3 x Gigabit LAN Ethernet ports and USB 2.0 port provide warp speeds and flexible internet access
- EasyMesh: Provides whole-home Wi-Fi coverage with standard mesh technology
- Telephony: Make or receive phone calls over the internet simply
- Easy Setup: Set up your router in minutes with the powerful TP-Link Aginet App
- TR-069 & TR-369 Remote Management: TR-098, TR-181, TR-111, and TR-143 are supported
- Wi-Fi 6, 2.4 GHz and 5 GHz, 1201 Mbps at 5 GHz, 199.7 x 148.6 x 67.5 mm, Internal Antennas



WAN connection		Security	
Ethernet WAN *	✓	Schedule access	✓
DSL WAN *	✓	DoS attack prevention	✓
SIM card slot *	✗	MAC address filtering	✓
3G/4G USB modem compatibility *	✗	IP address filtering	✓
WAN connection type	RJ-45	Protocols	
Wireless LAN features		DHCP client	✓
Wi-Fi band *	Dual-band (2.4 GHz / 5 GHz)	DHCP server	✗
Top Wi-Fi standard *	Wi-Fi 6 (802.11ax)	Supported network protocols	IPv4, IPv6
WLAN data transfer rate (max) *	1201 Mbit/s	Design	
Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac), Wi-Fi 6 (802.11ax)	Product colour	White
WLAN data transfer rate (first band)	574 Mbit/s	Wall mountable	✓
WLAN data transfer rate (second band)	1201 Mbit/s	LED indicators	Status
Network		On/off switch	✓
Ethernet LAN *	✓	Product type *	Tabletop router
Ethernet LAN interface type *	Gigabit Ethernet	Certificates	
Ethernet LAN data rates	10,100,1000 Mbit/s	Certification	THIS
Cabling technology	10/100/1000Base-T(X)	Packaging content	
Networking standards	IEEE 802.11ac, IEEE 802.11ax, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n	Cables included	LAN (RJ-45)
Static route	✓	AC adapter included	✓
USB sharing	✓	Quick installation guide	✓
Support Samba (storage)	✓	Antenna	
Media server	✓	Antenna design *	Internal
VPN support	PPTP, OpenVPN, IPSec	Transmit power	23 dBmW
		Power	
		Output voltage	12 V

Ports & interfaces		Power	
Ethernet LAN (RJ-45) ports *	3	Output current	1.5 A
USB port *	✓	Operational conditions	
USB 2.0 ports quantity	1	Operating temperature (T-T)	0 - 40 °C
Management features		Storage temperature (T-T)	-40 - 70 °C
Wi-Fi Multimedia (WMM)/(WME)	✓	Operating relative humidity (H-H)	10 - 90%
Wireless statistics	✓	Storage relative humidity (H-H)	5 - 90%
Reset button	✓	System requirements	
WPS push button	✓	Browser supported	Internet Explorer 11, Firefox 12.0, Chrome 20.0, Safari 4.0, or other Java-enabled browser
Intelligent Mesh technology	✓	Windows operating systems supported	Windows 10, Windows 2000, Windows 7, Windows 8, Windows 8.1, Windows 98, Windows NT, Windows Vista, Windows XP
MU-MIMO technology	✓	Mac operating systems supported	MacOS
Security		Weight & dimensions	
Security algorithms	WPA, WPA2, WPA3	Width	148.6 mm
Firewall	✓	Depth	199.7 mm
Stateful Packet Inspection (SPI)	✓	Height	67.5 mm



4897098684689



4897098685266

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.