Lenovo 4X67A72593 graphics card NVIDIA A40 48 GB GDDR6



Brand : Lenovo

Product code: 4X67A72593

Product name : 4X67A72593

ThinkSystem NVIDIA A40 48GB PCIe Gen4 Passive GPU w/o CEC

Lenovo 4X67A72593 graphics card NVIDIA A40 48 GB GDDR6:

The NVIDIA A40 is a powerful data center GPU for visual computing, delivering high performance and capabilities to professionals for graphics-based workloads such as ray traced rendering, high-performance virtual workstations, simulation, 3D design, VR, and virtual production. The A40 GPU is a graphics-based virtualization solution for designers, engineers, scientists, and creatives that need this performance from anywhere in the world.
Lenovo 4X67A72593. Graphics processor family: NVIDIA, Graphics processor: A40. Discrete graphics card memory: 48 GB, Graphics card memory type: GDDR6. DirectX version: 12.07, OpenGL version: 4.68. Interface type: PCI Express x16 4.0. Cooling type: Passive

Processor	
CUDA *	✔
CUDA cores	10752
Graphics processor family *	NVIDIA
Graphics processor *	A40

Memory	
Discrete graphics card memory *	48 GB
Graphics card memory type *	GDDR6
Memory bandwidth (max)	696 GB/s

Ports & interfaces	
Interface type *	PCI Express x16 4.0
DisplayPorts quantity *	3
DisplayPort version	1.4

Performance	
DirectX version *	12.07
Shader model version *	5.17
OpenGL version *	4.68

Design	
Cooling type *	Passive

Power	
Power consumption (max)	300 W

0889488571963

889488571963

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date