

Targus DOCK421GLZ mobile device dock station
Tablet/Smartphone Black

Brand : Targus

Product code: DOCK421GLZ

Product name : DOCK421GLZ

100W, HDMI, USB-A x 2, USB-C / 3.2 Gen 1, 0.09 kg

Targus DOCK421GLZ mobile device dock station Tablet/Smartphone Black:

Turn your DeX-enabled tablet or smartphone into a workstation. Add this Single Video HDMI Dock to the Targus Tablet Cradle Workstation (AWU201GLZ/AWU202GLZ/AWU314BGLZ sold separately) and enable your DeX device to connect to any HDMI monitor. The dock also features a Gigabit Ethernet port for a secure internet connection, and 2 USB-A 3.2 Gen 1 ports plus 1 USB-C 3.2 Gen 1 port to connect essential peripherals like a mouse, keyboard or additional hub.

Targus DOCK421GLZ. Basic device type: Tablet/Smartphone, Compatibility: AWU201GLZ, AWU202GLZ, AWU314BGLZ. Docking connector type: USB Type-C. Width: 123 mm, Depth: 66 mm, Height: 25 mm, Weight: 90 g. Product colour: Black



Performance		Ports & interfaces	
Basic device type *	Tablet/Smartphone	USB Power Delivery (USB PD)	✓
Compatibility	AWU201GLZ, AWU202GLZ, AWU314BGLZ	USB Power Delivery up to	100 W
Product colour	Black	Audio output *	✗
Maximum refresh rate	60 Hz	HDMI *	✓
Maximum resolution	1920 x 1200 pixels	HDMI connector type	Full-size
HD type	Full HD	HDMI ports quantity	1
Network		Ethernet LAN (RJ-45) ports	1
Bluetooth *	✗	Power	
Ethernet LAN	✓	Power source type	DC
Ports & interfaces		Power consumption (max)	100 W
Docking connector type *	USB Type-C	Weight & dimensions	
USB hub *	✓	Width	123 mm
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity	2	Depth	66 mm
USB Type-C ports quantity	1	Height	25 mm
		Weight	90 g



5051794032406

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.