



Lenovo 4XC7A08294 network card Internal Ethernet 25000 Mbit/s

Brand : Lenovo
Product code: 4XC7A08294
Product name : 4XC7A08294




ThinkSystem Intel E810-DA2 10/25GbE SFP28 2-Port OCP

Lenovo 4XC7A08294 network card Internal Ethernet 25000 Mbit/s:

The ThinkSystem Intel E810-DA2 and E810-DA4 10/25GbE SFP28 network adapters improve application efficiency and network performance with innovative and versatile capabilities. With two or four 25GbE SFP28 ports and key performance optimizations, the E810 adapters supports solutions across Cloud, Enterprise, and Communications.

This product guide provides essential presales information to understand the Intel E810 adapters and their key features, specifications and compatibility. This guide is intended for technical specialists, sales specialists, sales engineers, IT architects, and other IT professionals who want to learn more about the E810 adapters and consider their use in IT solutions.
Lenovo 4XC7A08294. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Maximum data transfer rate: 25000 Mbit/s

Ports & interfaces		Design	
Connectivity technology *	Wired	Certification	FCC B UL CE VCCI BSMI RCM KCC
Host interface *	PCI Express	Operational conditions	
Interface *	Ethernet	Operating temperature (T-T)	0 - 55 °C
PCI version	4.0	Storage temperature (T-T)	-40 - 70 °C
Network		Operating relative humidity (H-H)	10 - 90%
Maximum data transfer rate *	25000 Mbit/s	Weight & dimensions	
Ethernet interface type	10 Gigabit Ethernet, 25 Gigabit Ethernet	Width	76 mm
Design		Depth	115 mm
Component for *	Server		
Internal *	✓		



0889488518470



889488518470



5415247304166

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.