



Lenovo 400 mouse Office Ambidextrous RF Wireless Optical 2400 DPI

Brand : Lenovo

Product code: GY51D20865

Product name : 400

- Compact 4-button compact ambidextrous mouse
 - On-the-fly DPI switch (800 DPI, 1600 DPI, 2400 DPI)
 - Red optical sensor
 - Plug-and-play 2.4 GHz USB-C wireless dongle
 - 1 x AA battery, up to 18 months of battery life (may vary based on usage)
 - Supports Lenovo USB-A or USB-C Unified Pairing Receiver
 - Compatible with Windows and Chrome OS
- 400 USB-C Wireless Compact



Lenovo 400 mouse Office Ambidextrous RF Wireless Optical 2400 DPI:

With its compact, portable form, the Lenovo 400 USB-C Compact Wireless Mouse is perfect for your on-the-go lifestyle. Its convenient wireless USB-C receiver provides stable plug-and-play connectivity, while enabling you to pair your ultrabook with up to eight devices. Thanks to its red optical sensor and up to 2400 on-the-fly DPI adjustment, precision and accuracy is guaranteed whether you are working on a small or big screen.

Mouse		Power	
Number of scroll wheels	1	Number of batteries supported	1
Purpose *	Office	Battery type	AA
Device interface *	RF Wireless	Service life of battery	18 month(s)
Movement detection technology *	Optical	System requirements	
Movement resolution *	2400 DPI	Windows operating systems supported	Windows 11
Buttons type	Pressed buttons	Other operating systems supported	ChromeOS
Scroll type *	Wheel	Operational conditions	
Buttons quantity *	4	Operating temperature (T-T)	0 - 40 °C
Buttons durability (million clicks)	3	Operating relative humidity (H-H)	20 - 95%
Customizable movement resolution	✓	Weight & dimensions	
Number of movement resolution modes	3	Width	100 mm
Frequency band	2.4 GHz	Depth	58 mm
Certification	CB, cTUVus, FCC, IC, TÜV-certificering, CE, JRF, VCCI, GB/T 26245, IMDA, NBTC, DWLF & M, TRC, ANRT	Height	35 mm
		Weight	55 g
Design		Packaging data	
Form factor *	Ambidextrous	Quantity per pack *	1 pc(s)
Ergonomic design	✓	Package width	126 mm
Product colour *	Black	Package depth	94 mm
Power		Package height	47 mm
Power source *	Batteries	Package weight	132 g
		Package type	Box
Packaging content			
		Receiver included	✓
		Wireless receiver interface	USB Type-C



0195892016267



195892016267



0195892016854



195892016854

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.