

ASUS BR1100C-C1XA-3Y Intel® Celeron® N N4500 Laptop 29.5 cm (11.6") HD 4 GB DDR4-SDRAM 128 GB eMMC Wi-Fi 6 (802.11ax) Windows 11 Pro Academic Grey

Brand : ASUS

Product code: 90NX03B1-M00E50

Product name : BR1100C-C1XA-3Y

- Windows 11 Pro Education
- 4 GB memory
- 128 GB eMMC
- Ruggedized Design
- Dual-band Wi-Fi 6 (802.11ax)
- AI Noise Canceling
- TÜV Rheinland certified display

Intel Celeron N4500 (4MB Cache, 1.1GHz), 4GB DDR4-SDRAM, 128GB eMMC, 29.5 cm (11.6") HD 1366 x 768, Intel UHD Graphics, LAN, WLAN, Webcam, Windows 11 Pro Academic 64-bit
ASUS BR1100C-C1XA-3Y. Product type: Laptop, Form factor: Clamshell. Processor family: Intel® Celeron® N, Processor model: N4500, Processor frequency: 1.1 GHz. Display diagonal: 29.5 cm (11.6"), HD type: HD, Display resolution: 1366 x 768 pixels. Internal memory: 4 GB, Internal memory type: DDR4-SDRAM. Total storage capacity: 128 GB, Storage media: eMMC. On-board graphics card model: Intel® UHD Graphics. Operating system installed: Windows 11 Pro Academic. Product colour: Grey



Design		Network	
Colour name	Dark Grey	Antenna type	2x2
Product type *	Laptop	Ethernet LAN	✓
Product colour *	Grey	Ethernet LAN data rates	10,100,1000 Mbit/s
Form factor *	Clamshell	Bluetooth	✓
Housing material	Plastic	Bluetooth version	5.3
Display		Ports & interfaces	
Display diagonal *	29.5 cm (11.6")	USB 2.0 ports quantity *	1
Display resolution *	1366 x 768 pixels	USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity *	1
Touchscreen *	✗	USB 3.2 Gen 2 (3.1 Gen 2) Type-C ports quantity	1
HD type	HD	Ethernet LAN (RJ-45) ports	1
LED backlight	✓	HDMI ports quantity *	1
Native aspect ratio	16:9	HDMI version	1.4
Anti-glare screen	✓	Combo headphone/mic port	✓
Display brightness	200 cd/m²	Keyboard	
RGB colour space	NTSC	Pointing device	Touchpad
Colour gamut	45%	Numeric keypad *	✗
Processor		Software	
Processor manufacturer *	Intel	Operating system architecture	64-bit
Processor family *	Intel® Celeron® N	Operating system installed *	Windows 11 Pro Academic
Processor model *	N4500	Processor special features	
Processor cores	2	CPU configuration (max)	1
Processor boost frequency	2.8 GHz	Battery	
Processor frequency *	1.1 GHz	Battery technology	Lithium-Ion (Li-Ion)
Processor cache	4 MB	Number of battery cells	3
Processor cache type	Smart Cache		
Memory			
Internal memory *	4 GB		

Memory		Battery	
Internal memory type	DDR4-SDRAM	Battery capacity *	42 Wh
Memory form factor	On-board	Power	
Maximum internal memory *	4 GB	AC adapter power	45 W
Storage		AC adapter frequency	50 - 60 Hz
Total storage capacity *	128 GB	AC adapter input voltage	100 - 240 V
Storage media *	eMMC	AC adapter output current	2.37 A
Optical drive type *	✗	AC adapter output voltage	19 V
Graphics		DC-in jack	✓
Discrete graphics card model *	Not available	USB Type-C charging port *	✓
On-board graphics card *	✓	USB Power Delivery (USB PD)	✓
On-board GPU manufacturer	Intel	Security	
Discrete graphics card *	✗	Cable lock slot	✓
On-board graphics card model *	Intel® UHD Graphics	Cable lock slot type	Kensington
Audio		Trusted Platform Module (TPM)	✓
Audio system	SonicMaster	Trusted Platform Module (TPM) version	2.0
Built-in microphone	✓	Weight & dimensions	
Camera		Width	294.6 mm
Front camera	✓	Depth	204.9 mm
Front camera HD type	HD	Height (front)	1.99 cm
Privacy camera	✓	Height (rear)	2 cm
Privacy type	Privacy shutter	Weight *	1.26 kg
Network		Packaging content	
Top Wi-Fi standard *	Wi-Fi 6 (802.11ax)	AC adapter included *	✓
Wi-Fi standards	Wi-Fi 6 (802.11ax)		
Mobile network connection *	✗		



4711387084731



0197105084735



197105084735

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.