



APC Easy UPS 3S 20 kVA 400 V 3:1 UPS for internal batteries

Brand : APC

Product code: E3SUPS20K3IB

Product name : Easy UPS 3S 20 kVA 400 V 3:1 UPS for internal batteries

- Easy UPS 3S is easy to install and start up
 - Parallel up to 4 UPSs for capacity or redundancy
 - Extended runtime options available
 - EcoStruxure IT: Enables resilient, secure, and sustainable IT environments
- Easy UPS 3S 20 kVA 400 V 3:1 UPS for internal batteries

APC Easy UPS 3S 20 kVA 400 V 3:1 UPS for internal batteries:


This high-efficiency 3-phase UPS E3SUPS20K3IB features advanced product features, competitive specifications, and robust electrical design, making business continuity easy in the data center or electrical room. This is an exceptionally easy to install, operate, maintain, and service 20 kVA UPS, ideal for small and medium businesses. Includes dust filter and conformance-coated boards for harsh environments. This UPS is for internal batteries, but is supplied without batteries, so you can easily customize the battery runtime.



Features		Design	
UPS topology *	Double-conversion (Online)	International Protection (IP) code	IP20
Output power capacity *	20 kVA	Operational conditions	
Output power *	20000 W	Operating temperature (T-T)	0 - 40 °C
Input operation voltage (min) *	304 V	Storage temperature (T-T)	-25 - 55 °C
Input operation voltage (max) *	477 V	Operating relative humidity (H-H)	0 - 95%
Input frequency *	45/65 Hz	Storage relative humidity (H-H)	0 - 95%
Output operation voltage (min)	220 V	Certificates	
Output operation voltage (max)	240 V	Compliance certificates	RoHS
Output frequency	50/60 Hz	Certification	CE, EAC, IEC 62040-1-1, IEC 62040-2, IEC 62040-3, IEC 62040-4, ISTA 2B, RCM, WEEE
Maximum current	37 A	Weight & dimensions	
Power factor	0.99	Width	380 mm
Crest factor	3:1	Depth	907 mm
Output voltage Total Harmonic Distortion (THD)	5.5%	Height	1400 mm
Battery		Weight	150 kg
Battery technology	Sealed Lead Acid (VRLA)	Packaging data	
Battery voltage	240 V	Package width	563 mm
Design		Package depth	1014 mm
Form factor *	Rackmount	Package height	1640 mm
Product colour *	White	Package weight	158 kg
		Logistics data	
		Harmonized System (HS) code	85078000



0731304340775



731304340775

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.