



AOC 24P3CV computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD LED Black

Brand : AOC

Product code: 24P3CV

Product name : 24P3CV

Screen size (inch) 23.8, Panel resolution 1920x1080, Max Refresh rate 100 Hz, Panel type IPS, USB-C connectivity USB-C 3.2 x 1 (DP alt mode, upstream, power delivery up to 65 W), HDMI HDMI 1.4 x 1, DisplayPort DisplayPort 1.4 x 1, Sync technology (VRR) Adaptive Sync
AOC 24P3CV. Display diagonal: 60.5 cm (23.8"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LED, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ergonomics	
Display diagonal *	60.5 cm (23.8")	Cable lock slot *	✓
Display resolution *	1920 x 1080 pixels	Cable lock slot type	Kensington
HD type *	Full HD	Height adjustment *	✓
Native aspect ratio *	16:9	Adjustable height (max)	15 cm
Display technology *	LED	Pivot	✓
Panel type *	IPS	Pivot angle	-90 - 90°
LED backlight	✓	Swivelling	✓
Backlight type	W-LED	Swivel angle range	180 - 180°
Touchscreen *	✗	Tilt adjustment	✓
Display brightness (typical)	300 cd/m²	Tilt angle range	-5 - 35°
Response time *	4 ms	On Screen Display (OSD)	✓
Response time measurement type	GTG (Gray to Gray)	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, Dutch, English, Finnish, French, German, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish, Swedish
Anti-glare screen	✓		
Screen shape *	Flat		
Contrast ratio (typical) *	1000:1	Number of OSD languages	16
Contrast ratio (dynamic)	50000000:1	Power	
Maximum refresh rate *	100 Hz	Energy efficiency class (SDR) *	E
Viewing angle, horizontal	178°	Energy efficiency class (HDR) *	E
Viewing angle, vertical	178°	Energy consumption (SDR) per 1000 hours *	18 kWh
Display number of colours *	16.7 million colours	Energy consumption (HDR) per 1000 hours *	18 kWh
Pixel pitch	0.2745 x 0.2745 mm	Power consumption (typical) *	14.5 W
Pixel density	93 ppi	Power consumption (standby) *	0.5 W
Digital horizontal frequency	30 - 85 kHz	Power consumption (off)	0.3 W
Digital vertical frequency	48 - 100 Hz	AC input voltage	100 - 240 V
Display diagonal (metric)	60.5 cm		
High Dynamic Range (HDR) supported	✓		
Surface hardness	3H		
sRGB coverage (typical)	124.3%		

Performance		Power	
Fast charging	✓	AC input frequency	50/60 Hz
Flicker-free technology	✓	Power supply type	Internal
Low Blue Light technology	✓	Energy efficiency scale	A to G
Multimedia		Weight & dimensions	
Number of speakers	2	Width (with stand)	540 mm
RMS rated power	4 W	Depth (with stand)	200.1 mm
Built-in speaker(s) *	✓	Height (with stand)	502.9 mm
Built-in camera *	✗	Weight (with stand)	5.37 kg
Design		Width (without stand)	540 mm
Market positioning *	Office	Depth (without stand)	50.7 mm
Product colour *	Black	Height (without stand)	326.3 mm
Front bezel colour	Black	Weight (without stand)	3.66 kg
Detachable stand	✓	Packaging data	
Ports & interfaces		Package width	613 mm
Built-in USB hub *	✓	Package depth	162 mm
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Package height	519 mm
USB upstream port type	USB Type-C	Package weight	8.31 kg
Number of upstream ports	1	USB cable length	1.8 m
USB Type-A downstream ports quantity	4	Packaging content	
USB Type-C DisplayPort Alternate Mode	✓	Cables included	AC, HDMI, DisplayPort, USB Type-C
USB Power Delivery (USB PD)	✓	DisplayPort cable length	1.8 m
USB Power Delivery up to	65 W	HDMI cable length	1.8 m
HDMI *	✓	Power cable length	1.8 m
HDMI ports quantity	1	Sustainability	
HDMI version	1.4	Sustainability certificates	EPEAT Gold, TCO
DisplayPorts quantity	1	Doesn't contain	Mercury, PVC/BFR
DisplayPort out quantity	1	Other features	
DisplayPort version	1.2	Compatibility	VESA-P2
Audio output	✓	Local dimming	✓
Headphone out *	✓	Exterior finish type	Textured
Headphone outputs	1	Heavy metals free	Hg (mercury)
Headphone connectivity	3.5 mm	Bezel thickness type	Frameless
Built-in KVM switch	✓	Warranty period	3 year(s)
Network		Compliance certificates	CE
Ethernet LAN	✓	Mean time between failures (MTBF)	70000 h
Ergonomics		Certification	WEEE,REACH compliant,RoHs compliant,HF,CB,TUV-GS-Mark,ISO 9241-307,EAC,FCC
VESA mounting *	✓	Recycling data	
Panel mounting interface	100 x 100 mm	Recyclable packaging material	100%
		Post-consumer recycled plastic	85%
		Recycled content in packaging	100%



4038986140751

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.