
Lenovo 4Y37A72482 RAID controller PCI Express x8 3.0 12 Gbit/s



Brand : Lenovo

Product code: 4Y37A72482

Product name : 4Y37A72482

ThinkSystem RAID 5350-8i

Lenovo 4Y37A72482 RAID controller PCI Express x8 3.0 12 Gbit/s:

The ThinkSystem RAID 5350-8i adapter is an entry-level 12 Gb SAS/SATA internal RAID adapter that offers a cost-effective RAID solution for small to medium business customers. This cacheless adapter supports RAID levels 0/1/10/5/50, and include support for Lenovo management tools.

This product guide provides essential presales information to understand the ThinkSystem RAID 5350-8i adapter and its key features, specifications, and compatibility. This guide is intended for technical specialists, sales specialists, sales engineers, IT architects, and other IT professionals who want to learn more about the RAID adapter and consider its use in IT solutions.
Lenovo 4Y37A72482. Supported storage drive interfaces: SAS, Serial ATA, Host interface: PCI Express x8. RAID levels: 0, 1, 5, 10, 50, Data transfer rate: 12 Gbit/s, Chipset: Adaptec PM8222 SmartIOC 2100. Width: 167 mm, Height: 64 mm

Ports & interfaces	
Supported storage drive interfaces *	SAS, Serial ATA
Host interface *	PCI Express x8
PCI Express slots version	3.0
Internal mini-SAS HD ports	2

Performance	
RAID levels *	0, 1, 5, 10, 50
Data transfer rate	12 Gbit/s
Chipset	Adaptec PM8222 SmartIOC 2100
JBOD function	✔
S.M.A.R.T. support	✔
Hot-swap	✔

Performance	
Certification	FCC Part 15 Class A Australia/New Zealand (AS/NZS 3548) Canada (ICES-003 Class B) Europe (EN55032/EN55024) Japan VCCI Korea KCC RoHS compliant EN/IEC/UL 60950 USA (FCC 47 CFR part 15 Subpart B class B)

Operational conditions	
Operating temperature (T-T)	0 - 55 °C
Operating relative humidity (H-H)	20 - 80%

Weight & dimensions	
Width	167 mm
Height	64 mm

889488588008

0889488588008

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date