3M PF490W3E display privacy filter 124.5 cm (49") Monitor Frameless display privacy filter

Brand : 3M

Product code: PF490W3E

Product name : PF490W3E

3M™ Privacy Filter for 49in Full Screen Monitor, 32:9, PF490W3E

3M PF490W3E display privacy filter 124.5 cm (49") Monitor Frameless display privacy filter:

3M™ Privacy Filters provide world-class "black out" privacy from side views outside the 60-degree viewing angle, while creating an excellent viewing experience from straight on views. Designed for full screen monitors with flat glass displays, these privacy filters are reversible between a glossy side and a glare-reducing matte side that helps reduce reflections and hide fingerprints, so you can enjoy pristine image clarity.
3M PF490W3E. Maximum screen size: 124.5 cm (49"). Aspect ratio: 32:9. Suitable for: Monitor, Type: Frameless display privacy filter. Limits viewing angle: 60°. Weight: 260.36202038 g

Design	
Maximum screen size *	124.5 cm (49")
Suitable for *	Monitor
Type *	Frameless display privacy filter
Screen size HxW	1212 x 343 mm
Display diagonal (metric)	124.6 cm
Product colour	Black

Features	
Display filter features *	Anti-glare, Privacy
Aspect ratio	32:9
Widescreen	✔
Scratch-resistant	✔
Limits viewing angle	60°
Durable screen protection	✔
Privacy filtering orientation	Landscape
Touchscreen compatible	✔
Reduces blue light up to	35%
Blue light filter	✔

Weight & dimensions	
Width	1212 mm
Height	343 mm
Weight	260.36202038 g

Packaging data	
Package width	1270 mm
Package depth	7.29 mm
Package height	863.6 mm
Package weight	940.75057538 g

Logistics data	
Pallet net height	120.7 cm
Pallet net length	161.3 cm
Pallet net width	109.2 cm
Pallet net weight	57.3 kg
Pallet weight (EU)	288.5 kg
Products per pallet (EU)	220 pc(s)
Harmonized System (HS) code	85299097
Shipping (inner) case width	41.9 cm
Shipping (inner) case length	128.3 cm
Shipping (inner) case height	4.92 cm
Shipping (inner) case gross weight	5.88 kg
Shipping (inner) case net weight	1.3 kg
Products per shipping (inner) case	5 pc(s)
Shipping (inner) case GTIN (EAN/UPC)	51128011072



0051128011072



051128011072



Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date