

ASUS GT730-4H-SL-2GD5 NVIDIA GeForce GT 730 2 GB GDDR5

Brand : ASUS

Product code: 90YV0H20-M0NA00

Product name : GT730-4H-SL-2GD5

- 4x HDMI Ports enable multi-monitor productivity on up to 4 displays
 - Single-slot Design fits in small chassis and leaves room for additional PCIe devices
 - Passive Cooling keeps things quiet
 - Auto-Extreme Technology uses automation to enhance reliability
 - GPU Tweak II provides intuitive performance tweaking, thermal controls, and system monitoring
- GeForce GT 730, 2GB GDDR5, PCI Express x1, 4x HDMI, HDCP, 148x105x18 mm
 ASUS GT730-4H-SL-2GD5. Graphics processor family: NVIDIA, Graphics processor: GeForce GT 730.
 Discrete graphics card memory: 2 GB, Graphics card memory type: GDDR5, Memory clock speed: 5010 MHz. Maximum resolution: 3840 x 2160 pixels. OpenGL version: 4.6. Interface type: PCI Express x1.
 Cooling type: Passive



Processor		Performance	
CUDA *	✓	TV tuner integrated *	✗
CUDA cores	384	OpenGL version *	4.6
Graphics processor family *	NVIDIA	HDCP	✓
Graphics processor *	GeForce GT 730	Dual Link DVI *	✗
Processor boost clock speed	902 MHz	Design	
Processor boost clock speed (OC mode)	927 MHz	Cooling type *	Passive
Maximum resolution *	3840 x 2160 pixels	Number of slots	1
Parallel processing technology support *	Not supported	Product colour	Black, Blue
Maximum displays per videocard	4	Power	
Memory		Minimum system power supply *	300 W
Discrete graphics card memory *	2 GB	Weight & dimensions	
Graphics card memory type *	GDDR5	Length	148 mm
Memory clock speed	5010 MHz	Depth	18 mm
Ports & interfaces		Height	105 mm
Interface type *	PCI Express x1	Packaging data	
HDMI ports quantity *	4	Package type	Box
HDMI version	1.4b	Packaging content	
		Manual	✓
Logistics data			
		Harmonized System (HS) code	84733020



4711081369417



0195553377751



195553377751



0195553369411



195553369411

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.