

ASUS TUF GAMING B550M-PLUS WIFI II AMD B550 Socket AM4 micro ATX

Brand : ASUS

Product code: 90MB19Y0-M0EAY0

Product name : TUF GAMING B550M-PLUS WIFI II

- AMD AM4 socket: Ready for Ryzen™ 5000 Series/ 5000 G-Series/ 4000 G-Series/ 3000 Series Desktop Processors
 - Enhanced power solution: 8+2 DrMOS power stages, ProCool connector, military-grade TUF components, and DIGI+ VRM for maximum durability
 - Comprehensive cooling: VRM heatsinks, PCH fanless heatsink, M.2 heatsink, hybrid fan headers and Fan Xpert 2+ utility
 - Ultrafast connectivity: PCIe 4.0 M.2, USB 3.2 Gen 2 Type-A and Type-C® support
 - Made for online gaming: Wi-Fi 6, Realtek 2.5Gb Ethernet, and TUF LANGuard
 - Two-Way AI Noise Cancellation: Reduces background noise from the microphone and audio output for crystal-clear communication in games or video conferences
- microATX, AMD B550 chipset, AMD AM4 Socket, 4xDDR4 DIMM slots, 7.1 ch audio, 2.5-Gigabit LAN, Wi-Fi 6, Bluetooth 5.2, AMI UEFI BIOS



Processor		Rear panel I/O ports	
Processor manufacturer *	AMD	Ethernet LAN (RJ-45) ports *	1
Processor socket *	Socket AM4	PS/2 ports quantity	1
Compatible processor series *	AMD Ryzen 3000 Series, AMD Ryzen 5000 Series	HDMI ports quantity *	1
Supported processor sockets	Socket AM4	HDMI version	2.1
Memory Supported memory types * Number of memory slots * Memory slots type Memory channels ECC compatibility Supported memory clock speeds Maximum internal memory * Unbuffered memory	DDR4-SDRAM	DisplayPorts quantity	1
	4	DisplayPort version	1.2
	DIMM	Headphone outputs	5
	Dual-channel	Microphone in	✓
	ECC	S/PDIF out port	✓
	2133, 2400, 2666, 2800, 2933, 3000, 3200, 3333, 3400, 3466, 3600, 3733, 3866, 4000, 4133, 4200, 4266, 4333, 4400, 4466, 4600, 4800, 4866	WiFi-AP antenna jack	1
	128 GB	USB connector type	USB Type-A, USB Type-C
	✓	Network	
Storage controllers		Ethernet LAN	✓
Supported storage drive types	HDD & SSD	Ethernet interface type	2.5 Gigabit Ethernet
Supported storage drive interfaces *	M.2, PCI Express 3.0, PCI Express 4.0, SATA III	Wake-on-LAN ready	✓
Number of storage drives supported	6	Wi-Fi *	✓
RAID support	✓	Top Wi-Fi standard	Wi-Fi 6 (802.11ax)
RAID levels	0, 1, 10	Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac), Wi-Fi 6 (802.11ax)
Graphics		Bluetooth	✓
Parallel processing technology support *	Not supported	Bluetooth version	5.2
Maximum resolution	3840 x 2160 pixels	Features	
Internal I/O		Motherboard chipset *	AMD B550
USB 2.0 connectors *	2	Audio output channels *	7.1 channels
USB 3.2 Gen 1 (3.1 Gen 1) connectors *	1	Component for *	PC
Number of SATA III connectors *	4	Motherboard form factor *	micro ATX
Front panel audio connector	✓	Motherboard chipset family *	AMD
ATX Power connector (24-pin)	✓	Windows operating systems supported	Windows 10 x64, Windows 11
CPU fan connector	✓		
Number of chassis fan connectors	2		
EPS power connector (8-pin)	✓		
Number of COM connectors	1		

Internal I/O		Expansion slots	
TPM connector	✓	PCI Express x1 (Gen 3.x) slots	1
12V power connector	✓	PCI Express x16 (Gen 3.x) slots	1
RGB LED pin header	✓	PCI Express x16 (Gen 4.x) slots	1
Rear panel I/O ports		Number of M.2 (M) slots	2
USB 2.0 ports quantity *	2	BIOS	
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity *	4	BIOS type *	UEFI AMI
USB 3.2 Gen 2 (3.1 Gen 2) Type-A ports quantity *	1	BIOS memory size	256 Mbit
USB 3.2 Gen 2 (3.1 Gen 2) Type-C ports quantity *	1	Clear CMOS jumper	✓
		Logistics data	
		Harmonized System (HS) code	84733020
		Weight & dimensions	
		Width	244 mm
		Depth	244 mm
		Height	67 mm
		Packaging content	
		Cables included	SATA
		Drivers included	✓
		Other features	
		Weight	845 g



4711081305705

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.