

ASUS TUF Gaming VG24VQR computer monitor 59.9 cm (23.6") 1920 x 1080 pixels Full HD LED Black

Brand : ASUS

Product family: TUF Gaming

Product code: 90LM0577-B01170

Product name : VG24VQR

- 23.6-inch Full HD (1920 x 1080) 1500R gaming monitor with ultrafast 165Hz refresh rate designed for professional gamers and immersive gameplay
- Full HD(1920 X 1080)@120Hz output on PS5 & Xbox Series X/S
- ASUS Extreme Low Motion Blur (ELMB™) technology enables a 1ms response time (MPRT) together with Adaptive-sync, eliminating ghosting and tearing for sharp gaming visuals with high frame rates
- FreeSync Premium technology to eliminate screen tearing and choppy frame rates
- Features an ergonomically designed stand to offer extensive swivel, tilt, pivot and height adjustments
- Supports both Adaptive-Sync with NVIDIA GeForce* graphics cards and FreeSync with AMD Radeon graphics cards *Compatible with NVIDIA GeForce GTX 10 series, GTX 16 series, RTX 20 series and newer graphics cards

TUF Gaming VG24VQR Curved Gaming Monitor – 23.6 inch Full HD (1920 x 1080), 165Hz, Extreme Low Motion Blur™, FreeSync™ Premium, 1ms (MPRT), Shadow Boost



Display		Ergonomics	
Display diagonal *	59.9 cm (23.6")	VESA mounting *	✓
Display resolution *	1920 x 1080 pixels	Panel mounting interface	100 x 100 mm
HD type *	Full HD	Cable lock slot *	✓
Native aspect ratio *	16:9	Cable lock slot type	Kensington
Display technology *	LED	Height adjustment *	✓
Panel type *	VA	Adjustable height (max)	15 cm
Touchscreen *	✗	Pivot	✓
Display brightness (typical)	350 cd/m²	Pivot angle	-90 - 90°
Response time *	1 ms	Swivelling	✓
Screen shape *	Flat	Swivel angle range	-62 - 62°
Contrast ratio (typical) *	3000:1	Tilt adjustment	✓
Maximum refresh rate *	165 Hz	Tilt angle range	-5 - 23°
Viewing angle, horizontal	178°	Power	
Viewing angle, vertical	178°	Energy efficiency class (SDR) *	F
Display number of colours *	16.78 million colours	Energy consumption (SDR) per 1000 hours *	22 kWh
Performance		Power consumption (typical) *	20.5 W
NVIDIA G-SYNC *	✗	Power consumption (off)	0.5 W
AMD FreeSync *	✓	AC input voltage	100 - 240 V
AMD FreeSync type	FreeSync Premium	AC input frequency	50 - 60 Hz
Multimedia		Energy efficiency scale	A to G
Built-in speaker(s) *	✓	Weight & dimensions	
Built-in camera *	✗	Width (with stand)	537.6 mm
Design		Depth (with stand)	217.6 mm
Market positioning *	Gaming	Weight (with stand)	5.66 kg
Product colour *	Black	Width (without stand)	537.6 mm
Ports & interfaces		Depth (without stand)	65.3 mm
DVI port	✗	Height (without stand)	320.1 mm
HDMI *	✓	Weight (without stand)	4.8 kg

Ports & interfaces		Packaging data	
HDMI ports quantity	2	Package width	709 mm
HDMI version	1.4	Package depth	403 mm
DisplayPorts quantity	1	Package height	211 mm
DisplayPort version	1.2	Package weight	7.46 kg
Audio input	✗	Logistics data	
Headphone out *	✗	Harmonized System (HS) code	85285210
HDCP	✓		



4718017881708

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.