

ASUS ProArt PA147CDV computer monitor 35.6 cm (14") 1920 x 550 pixels LCD Touchscreen Black

Brand : ASUS

Product family: ProArt

Product code: 90LM0720-B01170

Product name : PA147CDV



- 14-inch, 32:9 Full HD (1920 x 550) IPS panel with 10-point multitouch and Microsoft Pen Protocol 2.0 support
 - Calman Verified and factory calibrated to Delta E < 2 for exceptional color accuracy, with 100% sRGB and 100% Rec. 709 coverage
 - ASUS Dial and Control Panel provide shortcuts in supported Adobe creative software
 - Patented mechanical kickstand design folds out smoothly and props the display up in portrait or landscape orientation to fit different creator's scenario
 - Includes one standard HDMI® and two USB Type-C® (DP Alt mode) ports for variety devices connection
 - ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience
- ASUS ProArt Display PA147CDV Creative Tool – 14-inch, 32:9, IPS, Full HD (1920 x 550), 100% sRGB, 100% Rec.709, Color Accuracy ΔE < 2, Calman Verified, USB-C, 10-point Touch, MPP2.0, ASUS Dial, Control Panel, Compatible with Adobe Software



Display		Ports & interfaces	
Display diagonal *	35.6 cm (14")	Built-in USB hub *	×
Display resolution *	1920 x 550 pixels	USB Type-C downstream ports quantity	2
Native aspect ratio *	32:9	USB Type-C DisplayPort Alternate Mode	✓
Display technology *	LCD	HDMI *	✓
Panel type *	IPS	HDMI ports quantity	1
Backlight type	LED	HDMI version	1.4
Touchscreen *	✓	Headphone out *	×
Display brightness (typical)	400 cd/m²	HDCP	✓
Response time *	5 ms	HDCP version	1.4
Display surface	Matt		
Anti-glare screen	✓		
Screen shape *	Flat		
Contrast ratio (typical) *	1200:1		
Maximum refresh rate *	60 Hz		
Viewing angle, horizontal	178°		
Viewing angle, vertical	178°		
Display number of colours *	16.7 million colours		
Pixel pitch	0.179 x 0.179 mm		
Pixel density	143 ppi		
Viewable size, horizontal	34.4 cm		
Viewable size, vertical	9.86 cm		
Digital horizontal frequency	24 - 83 kHz		
Digital vertical frequency	23 - 60 Hz		
Colour gamut standard	DCI-P3		
sRGB coverage (typical)	100%		
Performance		Ergonomics	
Flicker-free technology	✓	Pivot	✓
Low Blue Light technology	✓	Pivot angle	0 - 90°
		Tilt adjustment	✓
		Tilt angle range	25 - 70°
		Power	
		Energy efficiency class (SDR) *	E
		Energy consumption (SDR) per 1000 hours *	9 kWh
		Power consumption (typical) *	10 W
		Power consumption (PowerSave)	0.5 W
		AC input voltage	100 - 240 V
		AC input frequency	50 - 60 Hz
		Energy efficiency scale	A to G
		Weight & dimensions	
		Width (with stand)	357.2 mm

Multimedia		Weight & dimensions	
Number of speakers	2	Depth (with stand)	20.7 mm
RMS rated power	2 W	Height (with stand)	127.7 mm
Built-in speaker(s) *	✓	Weight (with stand)	950 g
Built-in camera *	✗	Packaging data	
Design		Package width	440 mm
Market positioning *	Graphics design	Package depth	92 mm
Product colour *	Black	Package height	290 mm
		Package weight	2.3 kg
		Package type	Box



4711081218265



0195553388047



195553388047

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.