



BenQ W5700 Standard throw projector 1800 ANSI lumens DLP UHD 4K (3840x2160) Black

Brand : BenQ

Product code: 9H.JKV77.17E

Product name : W5700

- True 4K UHD resolution with 8.3M pixels
- BenQ CinematicColor™ for cinema industry's 100% DCI-P3/Rec.709 color space
- HDR-PRO™ projector-optimized HDR technology (HDR10/HLG support)
DLP, 3840x2160, 1800 lum, 60-200/300", HDMI, USB, LAN, RS-232, DC 12V, IR, HDR, 100-240V AC, 492x168x349 mm

BenQ W5700. Projector brightness: 1800 ANSI lumens, Projection technology: DLP, Projector native resolution: UHD 4K (3840x2160). Light source type: Lamp, Service life of light source: 4000 h, Service life of light source (economic mode): 10000 h. Focus: Manual, Focal length range: 14.3 - 22.9 mm, Aperture range (F-F): 1.81 - 2.1. Supported graphics resolutions: 640 x 480 (VGA), 720 x 400, 800 x 600 (SVGA), 832 x 624, 1024 x 576 (WSVGA), 1024 x 768 (XGA),..., Supported video modes: 480i, 480p, 576i, 576p, 720p, 1080p, 2160p. Serial interface type: RS-232, HDMI connector type: Full-size, HDMI version: 2.0b



Projector		Network	
Screen size compatibility *	1524 - 7620 mm (60 - 300")	Ethernet LAN *	✓
Projection distance	1.75 - 9.32 m	Ethernet LAN (RJ-45) ports	1
Contrast ratio (dynamic)	100000:1	Wi-Fi *	✗
Projector brightness *	1800 ANSI lumens	Storage	
Projection technology *	DLP	Card reader integrated *	✗
Projector native resolution *	UHD 4K (3840x2160)	Features	
Native aspect ratio *	16:9	Noise level (economic mode)	26 dB
Number of colours	1.073 billion colours	HDCP	✓
Horizontal scan range	15 - 102 kHz	On Screen Display (OSD)	✓
Vertical scan range	23 - 120 Hz	On Screen Display (OSD) languages	Arabic, Bulgarian, Simplified Chinese, Traditional Chinese, Croatian, Czech, Danish, German, English, Spanish, Finnish, French, Greek, Hindi, Hungarian, Indonesian, Italian, Japanese, Korean, Norwegian, Polish, Portuguese, Romanian, Russian, Swedish, Thai, Turkish
Keystone correction, vertical	-40 - 40°		
Light source		Number of OSD languages	28
Light source type *	Lamp	Noise level *	32 dB
Service life of light source *	4000 h	Multimedia	
Service life of light source (economic mode)	10000 h	Built-in speaker(s) *	✗
Lamp power	245 W	Design	
Lens system		Market positioning *	Home cinema
Focus *	Manual	Product type *	Standard throw projector
Focal length range	14.3 - 22.9 mm	Product colour *	Black
Aperture range (F-F)	1.81 - 2.1	Placement	Desktop, Ceiling
Zoom capability	✓		
Zoom ratio	1.6:1		
Throw ratio	1.36 - 2.18		
Horizontal lens shift range	-23 - 23%		
Vertical lens shift range	-60 - 60%		
Video			
Full HD *	✓		

Video		Display	
Supported graphics resolutions	640 x 480 (VGA), 720 x 400, 800 x 600 (SVGA), 832 x 624, 1024 x 576 (WSVGA), 1024 x 768 (XGA), 1152 x 864 (XGA+), 1152 x 870, 1280 x 1024 (SXGA), 1280 x 720 (HD 720), 1280 x 768 (WXGA), 1280 x 800 (WXGA), 1280 x 960, 1360 x 768 (WXGA), 1400 x 1050 (SXGA+), 1440 x 900 (WXGA+), 1920 x 1080 (HD 1080), 1920 x 1200 (WUXGA), 3840 x 2160	Built-in display *	✗
		Power	
		Power source *	AC
		Power consumption (typical) *	330 W
		Power consumption (standby) *	0.5 W
		Power consumption (max)	405 W
Supported video modes	480i, 480p, 576i, 576p, 720p, 1080p, 2160p	Power consumption (economy mode)	247 W
		AC input voltage	100 - 240 V
Ports & interfaces		Operational conditions	
HDMI connector type	Full-size	Operating temperature (T-T)	0 - 40 °C
HDMI version	2.0b	Storage temperature (T-T)	-20 - 60 °C
USB 2.0 ports quantity	2	Operating relative humidity (H-H)	10 - 90%
Mini-USB 2.0 ports quantity	1	Storage relative humidity (H-H)	10 - 90%
USB 3.2 Gen 1 (3.1 Gen 1) Type-A ports quantity	1	Operating altitude	0 - 1499 m
		Weight & dimensions	
Serial interface type *	RS-232	Width	492 mm
PC Audio out	✓	Depth	349 mm
HDMI ports quantity *	2	Height	168 mm
DVI port *	✗	Weight *	6.5 kg
Mobile High-Definition Link (MHL)	✗	Packaging content	
AC (power) in	✓	Remote control included *	✓
DC-in jack	✓	Cables included	AC
Network		Manual	✓
Smart TV *	✗	Other features	
		Security updates end date	31/12/2024



4718755077593

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.