



BenQ MX825STH Short throw projector 3500 ANSI lumens DLP XGA (1024x768) White

Brand : BenQ

Product code: 9H.JMV77.13E

Product name : MX825STH



- 0.61 Short Throw Ratio

- SmartEco Power Saving Technology

- PointWrite Interactive Solution Compatible

DLP, 3500AL, XGA(1024X768), 4:3, 20000:1, 1 x 10W, 2 x D-sub in, D-sub out, RCA, S-Video in, 2 x HDMI, USB Type A, Mini USB Type B, RS232, RJ45, 260W, 33/29 dBA, 2.6 Kg

BenQ MX825STH. Projector brightness: 3500 ANSI lumens, Projection technology: DLP, Projector native resolution: XGA (1024x768). Light source type: Lamp, Service life of light source: 6000 h, Service life of light source (economic mode): 10000 h. Zoom type: Fixed, Offset: 115%. Supported graphics resolutions: 640 x 480 (VGA), 1024 x 768 (XGA), 1920 x 1200 (WUXGA), Supported video modes: 480i, 480p, 576i, 576p, 720p, 1080i, 1080p. Serial interface type: RS-232, HDMI connector type: Full-size



Projector		Network	
Screen size compatibility *	1524 - 3048 mm (60 - 120")	Smart TV *	✗
Projector brightness *	3500 ANSI lumens	Ethernet LAN *	✓
Projection technology *	DLP	Ethernet LAN (RJ-45) ports	1
Projector native resolution *	XGA (1024x768)	Wi-Fi *	✗
Contrast ratio (typical) *	20000:1	Storage	
Native aspect ratio *	4:3	Card reader integrated *	✗
Number of colours	1.073 billion colours	Features	
Horizontal scan range	15 - 102 kHz	Noise level (economic mode)	29 dB
Vertical scan range	23 - 120 Hz	On Screen Display (OSD)	✓
Keystone correction, vertical	-30 - 30°	On Screen Display (OSD) languages	Arabic, Bulgarian, Simplified Chinese, Traditional Chinese, Croatian, Czech, Danish, German, Dutch, English, Spanish, Finnish, French, Greek, Hindi, Hungarian, Indonesian, Italian, Japanese, Korean, Norwegian, Polish, Portuguese, Romanian, Russian, Swedish, Thai, Turkish
Matrix size	1.4 cm (0.55")	Number of OSD languages	27
Matrix type	DMD	Noise level *	33 dB
Light source		Air filter	✓
Light source type *	Lamp	Multimedia	
Service life of light source *	6000 h	Built-in speaker(s) *	✓
Service life of light source (economic mode)	10000 h	RMS rated power	10 W
Lens system		Number of built-in speakers	1
Zoom capability	✓	Design	
Zoom type	Fixed	Market positioning *	Short throw
Throw ratio	0.61	Product type *	Short throw projector
Offset	115%		
Video			
Supported graphics resolutions	640 x 480 (VGA), 1024 x 768 (XGA), 1920 x 1200 (WUXGA)		
Supported video modes	480i, 480p, 576i, 576p, 720p, 1080i, 1080p		

Ports & interfaces		Design	
HDMI connector type	Full-size	Product colour *	White
S-Video inputs quantity	1	Placement	Desktop
USB 2.0 ports quantity	1	Display	
USB 2.0 Type-B ports quantity	1	Built-in display *	✗
Audio (L/R) in *	1	Power	
Headphone outputs	1	Power source *	AC
Microphone in	✓	Power consumption (typical) *	260 W
Serial interface type *	RS-232	Power consumption (standby) *	0.5 W
PC in (D-Sub)	✓	AC input voltage	100 - 240 V
VGA (D-Sub) ports quantity *	3	AC input frequency	50 - 60 Hz
HDMI ports quantity *	2	Weight & dimensions	
Composite video in *	1	Width	296 mm
Component video (YPbPr/YCbCr) in *	2	Depth	239 mm
DVI port *	✗	Height	120 mm
		Weight *	2.6 kg
Packaging content			
		Remote control included *	✓
		Remote control type	IR
		Batteries included	✓
		Cables included	AC
		Manual	✓
Logistics data			
		Harmonized System (HS) code	85286200



4718755083792

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.