

ASUS BE24EQSB computer monitor 60.5 cm (23.8") 1920 x 1080 pixels Full HD LED Black

Brand : ASUS

Product code: 90LM05M1-B06370

Product name : BE24EQSB

- 60.5cm (23.8") Full HD 1920 x 1080 LED IPS

- 5ms, 16:9, 300cd/m², 1000:1

- USB, VGA, HDMI, DisplayPort

60.5cm (23.8") Full HD 1920 x 1080 LED IPS, 16:9, 300cd/m², 16.7M, 5ms, 178°/178°, 1000:1

ASUS BE24EQSB. Display diagonal: 60.5 cm (23.8"), Display resolution: 1920 x 1080 pixels, HD type: Full

HD, Display technology: LED, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal:

178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1

Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ports & interfaces	
Display diagonal *	60.5 cm (23.8")	HDCP	✓
Display resolution *	1920 x 1080 pixels	AC (power) in	✓
HD type *	Full HD	Ergonomics	
Native aspect ratio *	16:9	VESA mounting *	✓
Display technology *	LED	Panel mounting interface	100 x 100 mm
Panel type *	IPS	Cable lock slot *	✓
Backlight type	LED	Cable lock slot type	Kensington
Touchscreen *	✗	Height adjustment *	✓
Display brightness (typical)	300 cd/m²	Adjustable height (max)	13 cm
Response time *	5 ms	Pivot	✓
Screen shape *	Flat	Pivot angle	-90 - 90°
Contrast ratio (typical) *	1000:1	Swivelling	✓
Maximum refresh rate *	60 Hz	Swivel angle range	-180 - 180°
Viewing angle, horizontal	178°	Tilt adjustment	✓
Viewing angle, vertical	178°	Tilt angle range	-5 - 35°
Display number of colours *	16.7 million colours	Power	
Pixel pitch	0.2745 x 0.2745 mm	Energy efficiency class (SDR) *	D
Viewable size, horizontal	52.7 cm	Energy efficiency class (HDR) *	Not available
Viewable size, vertical	29.6 cm	Energy consumption (SDR) per 1000 hours *	14 kWh
Digital horizontal frequency	30 - 83 kHz	Power consumption (typical) *	11.2 W
Digital vertical frequency	47 - 76 Hz	Power consumption (off)	0 W
Performance		Power consumption (PowerSave)	0.5 W
NVIDIA G-SYNC *	✗	AC input voltage	100 - 240 V
AMD FreeSync *	✗	AC input frequency	50 - 60 Hz
Flicker-free technology	✓	Power supply type	Internal
Low Blue Light technology	✓	Energy efficiency scale	A to G
Multimedia			
Number of speakers	2		
RMS rated power	4 W		

Multimedia		Weight & dimensions	
Built-in speaker(s) *	✓	Width (with stand)	540 mm
Built-in camera *	✗	Depth (with stand)	211 mm
Design		Height (with stand)	462 mm
Market positioning *	Business	Weight (with stand)	7.8 kg
Product colour *	Black	Width (without stand)	540 mm
Frameless design	✓	Depth (without stand)	47 mm
Detachable stand	✓	Height (without stand)	330 mm
Feet colour	Black	Weight (without stand)	5 kg
Ports & interfaces		Packaging data	
Built-in USB hub *	✓	Package width	649 mm
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Package depth	192 mm
USB upstream port type	USB Type-B	Package height	474 mm
USB Type-A downstream ports quantity	4	Package weight	10.5 kg
VGA (D-Sub) ports quantity	1	Package type	Box
HDMI *	✓	Packaging content	
HDMI ports quantity	1	Stand included	✓
HDMI version	1.4	Cables included	AC, DisplayPort, HDMI, USB
DisplayPorts quantity	1	Quick start guide	✓
DisplayPort version	1.2	Sustainability	
Audio input	✓	Sustainability compliance	✓
Headphone out *	✓	Other features	
Headphone outputs	1	Certification	Energy Star TÜV Flicker-free TÜV Low Blue Light
Headphone connectivity	3.5 mm		



4718017562782

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.