

Epson Expression Photo XP-970 Inkjet A3 5760 x 1440 DPI 28 ppm Wi-Fi



Brand : Epson

Product family: Expression

Product code: C11CH45401

Product name : XP-970

- Compact and versatile: Print up to A3, scan and copy up to A4
- 6-colour Claria Photo HD Inks: Produce superior, long-lasting, glossy photos
- Wi-Fi & Wi-Fi Direct: Wireless printing with or without a network
- Easy mobile printing: Print easily from your smartphone or tablet2
- Dual paper trays: One for A4 and another for photo paper

A3, Automatic Duplex, CD/DVD print, 5760 x 1440 DPI, CIS Scanner, 1200 x 4800 DPI, Wi-Fi, USB, Ethernet

Epson Expression Photo XP-970. Print technology: Inkjet, Printing: Colour printing, Maximum resolution: 5760 x 1440 DPI, Print speed (colour, normal quality, A4/US Letter): 28 ppm. Copying: Colour copying. Scanning: Colour scanning, Optical scanning resolution: 1200 x 4800 DPI. Maximum ISO A-series paper size: A3. Wi-Fi. Direct printing. Product colour: Black

Printing		Network	
Duplex printing mode	Auto	Ethernet LAN *	✓
Print technology *	Inkjet	Security algorithms	64-bit WEP, 128-bit WEP, WPA-AES, WPA-PSK, WPA-TKIP
Printing *	Colour printing	Mobile printing technologies	Apple AirPrint, Epson Connect, Epson Email Print, Epson Remote Print, Epson iPrint, Google Cloud Print
Duplex printing *	✓		
Maximum resolution *	5760 x 1440 DPI		
Print speed (black, normal quality, A4/US Letter) *	28 ppm		
Print speed (colour, normal quality, A4/US Letter)	28 ppm		
Borderless printing	✓		
DVD/CD printing	✓		
Copying		Performance	
Copying *	Colour copying	Card reader integrated	✓
		Compatible memory cards	MicroSD (TransFlash), MicroSDHC, MicroSDXC, MiniSD, MiniSDHC, SD, SDHC, SDXC
Scanning		Design	
Scanning *	Colour scanning	Product colour *	Black
Optical scanning resolution *	1200 x 4800 DPI	Market positioning *	Home & office
Scan technology	CIS	Built-in display *	✓
Scan to	Cloud	Display	LCD
		Display diagonal	10.9 cm (4.3")
		Touchscreen	✓
		Control type	Touch
		Colour display	✓
Features		Power	
Printing colours *	Black, Cyan, Light Cyan, Light magenta, Magenta, Yellow	Power consumption (copying)	17 W
		Power consumption (sleep)	1.2 W
		AC input voltage	220 - 240 V
		AC input frequency	50 - 60 Hz
Input & output capacity		System requirements	
Total number of input trays *	2	Windows operating systems supported	✓
Paper input type	Paper tray	Mac operating systems supported	✓
Paper handling		Weight & dimensions	
Maximum ISO A-series paper size *	A3	Width	479 mm
Paper tray media types *	Envelopes, Glossy paper, Photo paper, Plain paper	Depth	356 mm
Multi-purpose tray media types	Envelopes, Glossy paper, Legal, Letter, Plain paper	Height	148 mm
ISO A-series sizes (A0...A9) *	A3, A4, A5, A6	Weight	8.7 kg
ISO B-series sizes (B0...B9)	B5		
Non-ISO print media sizes	Legal, Letter		
Envelopes sizes	10, C6, DL		
Photo paper sizes	10x15, 13x18 cm		

Ports & interfaces		Packaging content	
Direct printing *	✓	Cartridge(s) included	✓
USB port	✓	Power cord included	✓
Network		Warranty card	✓
Wi-Fi *	✓	Logistics data	
		Harmonized System (HS) code	84433100
Other features			
		PictBridge	✓
		Software CD	✓



8715946668321

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.