



DELL AB135418 USB flash drive 64 GB USB Type-A / USB Type-C 3.2 Gen 1 (3.1 Gen 1) Blue, Silver

Brand : DELL

Product code: AB135418

Product name : AB135418



- Supports Windows® 10, 8.1, 8, 7(SP1), Mac 10.9.x +, Linux 2.6 +, Chrome OS
 - Compatible with USB 2.0 and USB 3.0/USB 3.1 specification
 - Up to 100MB/s read and 15MB/s write speed
 - 64GB capacity
 - Expanded storage for tablets and smartphones with USB OTG support
 - Easily share files between mobile devices without the need for cables or Wi-Fi
 - Small form factor for easy portability
- 64GB USB 3.0 Type-A / Type-C

DELL AB135418 USB flash drive 64 GB USB Type-A / USB Type-C 3.2 Gen 1 (3.1 Gen 1) Blue, Silver:

The combo flash drive has a dual interface that works with both standard USB-A and USB Type-C™ ports. It's an ideal way to provide up to 64GB of extra storage for the latest smartphones, tablets, PCs and Mac computers, which may have limited expansion ports, and it's easier than sharing files via online services. It's plug and play and fast, with speeds up to 100MB/s read and 15MB/s write, and it has a rotating cap to protect the reversible USB Type-C connector.


Performance		Design	
Capacity *	64 GB	Product colour *	Blue, Silver
Device interface *	USB Type-A / USB Type-C	Security	
USB version *	3.2 Gen 1 (3.1 Gen 1)	Fingerprint reader	×
Read speed	100 MB/s	PIN-secured access	×
Write speed	15 MB/s	Password protection	×
Compatible operating systems	Windows® 10, 8.1, 8, 7(SP1), Mac 10.9.x +, Linux 2.6 +, Chrome OS	Packaging content	
Design		Quantity per pack	1 pc(s)
Form factor *	Swivel	Logistics data	
		Harmonized System (HS) code	84717070



5397184457184



0740617305586



740617305586

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.