

Display		Power	
High Dynamic Range (HDR) supported	✓	Energy efficiency scale	A to G
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10)	Weight & dimensions	
sRGB coverage (typical)	120%	Width (with stand)	709.8 mm
Performance		Depth (with stand)	243.3 mm
AMD FreeSync *	✓	Height (with stand)	507.1 mm
AMD FreeSync type	FreeSync Premium	Weight (with stand)	7.54 kg
Flicker-free technology	✓	Width (without stand)	709.8 mm
Low Blue Light technology	✓	Depth (without stand)	87.3 mm
Multimedia		Height (without stand)	426.2 mm
Number of speakers	2	Weight (without stand)	6.32 kg
RMS rated power	4 W	Packaging data	
Built-in speaker(s) *	✓	Package width	591 mm
Built-in camera *	✗	Package depth	803 mm
Design		Package height	223 mm
Market positioning *	Gaming	Package weight	10.2 kg
Product colour *	Black	Package type	Box
Front bezel colour	Black	Packaging content	
Feet colour	Black	Stand included	✓
Ports & interfaces		Cables included	AC, DisplayPort
DVI port	✗	Quick start guide	✓
HDMI *	✓	Other features	
HDMI ports quantity	2	Country of origin	China
HDMI version	2.0	Certification	TÜV Flicker-free TÜV Low Blue Light AMD FreeSync Premium
DisplayPorts quantity	1	Logistics data	
DisplayPort version	1.2	Harmonized System (HS) code	85285210



4718017988827

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.