



D-Link 24-port 10G SFP+, 4-port 10GBASE-T Smart Managed Switch



Brand : D-Link

Product code: DXS-1210-28S

Product name : D-Link 24-port 10G SFP+, 4-port 10GBASE-T Smart Managed Switch

- Access Control List
- IP-MAC-Port Binding
- Clientless MAC/Web Access Control
- D-Link Safeguard Engine
- Port Security
- ARP Spoofing Prevention

DXS-1210-28S - 24 x 10G SFP+, 4 x 10GBASE-T

D-Link 24-port 10G SFP+, 4-port 10GBASE-T Smart Managed Switch. Switch type: Managed, Switch layer: L2/L3. Basic switching RJ-45 Ethernet ports type: 10G Ethernet (100/1000/10000), Basic switching RJ-45 Ethernet ports quantity: 4, Console port: RJ-45. MAC address table: 32000 entries, Switching capacity: 560 Gbit/s. Networking standards: IEEE 802.3ab, IEEE 802.3ae, IEEE 802.3an, IEEE 802.3az, IEEE 802.3u, IEEE 802.3z. Rack mounting, Form factor: 1U

Management features		Security	
Switch type *	Managed	Access Control List (ACL) rules	256
Switch layer	L2/L3	IGMP snooping	✓
Quality of Service (QoS) support	✓	Protocols	
Web-based management	✓	Management protocols	SNMP v1/v2c/v3
Ports & interfaces		GARP VLAN Registration Protocol (GVRP)	✓
Basic switching RJ-45 Ethernet ports quantity *	4	Design	
Basic switching RJ-45 Ethernet ports type *	10G Ethernet (100/1000/10000)	Rack mounting *	✓
10G Ethernet (copper) ports quantity	4	Stackable *	✗
SFP+ module slots quantity	24	Form factor	1U
Console port	RJ-45	Product colour	Black
Network		LED indicators	Activity, Link, Speed
Networking standards *	IEEE 802.3ab, IEEE 802.3ae, IEEE 802.3an, IEEE 802.3az, IEEE 802.3u, IEEE 802.3z	Number of fans	2 fan(s)
10G support *	✓	Power	
Cable types supported	Cat6, Cat6a, Cat7	AC input voltage	100 - 240 V
Port mirroring	✓	Power consumption (max)	85.7 W
Flow control support	✓	Power over Ethernet (PoE)	
Link aggregation	✓	Power over Ethernet (PoE) *	✗
Auto MDI/MDI-X	✓	Operational conditions	
Spanning tree protocol	✓	Operating temperature (T-T)	-5 - 50 °C
VLAN support	✓	Storage temperature (T-T)	-20 - 70 °C
Number of VLANs	4094	Operating relative humidity (H-H)	0 - 95%
Data transmission		Storage relative humidity (H-H)	0 - 95%
		Weight & dimensions	
		Width	441 mm
		Depth	209.5 mm
		Height	44 mm
		Weight	3.27 kg
		Packaging content	
Switching capacity *	560 Gbit/s	Manual	✓
Throughput	416.64 Mpps	Certificates	
MAC address table *	32000 entries	Certification	CE Class A FCC Class A VCCI Class A IC BSMI
Store-and-forward	✓		
Jumbo frames support	✓		
Jumbo frames	9000		
Security			
Access Control List (ACL)	✓		

Logistics data

Harmonized System (HS) code	85176990
-----------------------------	----------



0790069456817



790069456817

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.