Epson Photo Paper Semigloss 200 White Semi-gloss



Brand : Epson

Product code: C13S450377

Product name : Photo Paper Semigloss 200

Production Photo Paper Semigloss 200 36" x 30m
Epson Photo Paper Semigloss 200. Finish type: Semi-gloss, Media weight: 200 g/m², Print technology: Inkjet. Roll width: 91.4 cm, Roll length: 30 m, Core diameter: 5.08 cm. Quantity per pack: 1 pc(s), Package width: 130 mm, Package depth: 960 mm. Country of origin: Germany

Features	
Print technology	Inkjet
Product colour	White
Finish type *	Semi-gloss
Media weight *	200 g/m²
Best uses	Photo, CAD, Production
Tint (L*a*b)	L* = 94 a* = 2 b* = -9.5 M0 (UV)
Paper brightness	2470
Printing media thickness	190 µm
Printing media gloss level	95

Features	
Compatible products	SureColor SC-T7200 (with Stand) SureColor SC-T5400M-MFP SureColor SC-T5400 SureColor SC-T5200 SureColor SC-T5100 Series SureColor SC-T3400 Series SureColor SC-T3200 (with stand) SureColor SC-T3100 Series SureColor SC-P9500 SureColor SC-P9000V SureColor SC-P9000 Violet Spectro SureColor SC-P9000 Series SureColor SC-P9000 STD Spectro SureColor SC-P9000 STD SureColor SC-P8000 Series SureColor SC-P8000 STD Spectro SureColor SC-P8000 STD SureColor SC-P7500 Spectro SureColor SC-P7500 SureColor SC-P7000V SureColor SC-P7000 Violet Spectro SureColor SC-P7000 Series SureColor SC-P7000 STD Spectro SureColor SC-P7000 STD SureColor SC-P6000 Series SureColor SC-P6000 STD Spectro SureColor SC-P6000 STD SureColor SC-P20000 SureColor SC-P10000 Epson Stylus Pro 9900 Epson Stylus Pro 9890
Operational conditions	
Operating temperature (T-T)	15 - 25 °C
Operating relative humidity (H-H)	35 - 65%
Weight & dimensions	
Roll width	91.4 cm
Roll length	30 m
Core diameter	5.08 cm
Packaging data	
Quantity per pack	1 pc(s)
Package width	130 mm
Package depth	960 mm
Package height	120 mm
Package weight	6.28 kg
Logistics data	
Harmonized System (HS) code	37032000
Other features	
Country of origin	Germany

8715946686905

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date