



APC SY16K48H-PD uninterruptible power supply (UPS) 16 kVA

Brand : APC

Product code: SY16K48H-PD

Product name : SY16K48H-PD

Symmetra PX 16kW All-In-One, Scalable to 48kW, 400V

APC SY16K48H-PD uninterruptible power supply (UPS) 16 kVA:

Hot-scalable power, runtime & distribution in a high-density single frame design. This high-efficiency 3-phase UPS scales as your data center grows up to 48kW/48kVA. Suitable for small & medium data center applications.

Includes: Network Management Card, Start-Up Service.
APC SY16K48H-PD. Output power capacity: 16 kVA, Noise level: 61 dB. AC outlet types: Hard Wire 5-wire (3P + N + E). Battery recharge time: 3 h. Product colour: Black. Certification: EN 50091-1,EN/IEC 62040-3,EN/IEC 62040-1-1,FCC Part 15 Class A,VFI-SS-111



Features		Operational conditions	
Output power capacity *	16 kVA	Operating altitude	0 - 999.9 m
Emergency Power Off (EPO)	✓	Non-operating altitude	0 - 15000 m
Noise level	61 dB	Certificates	
Audible alarm(s)	✓	Certification	EN 50091-1,EN/IEC 62040-3,EN/IEC 62040-1-1,FCC Part 15 Class A,VFI-SS-111
Ports & interfaces		Weight & dimensions	
AC outlet types	Hard Wire 5-wire (3P + N + E)	Weight	537 kg
Battery		Packaging data	
Battery recharge time	3 h	Package weight	578 kg
Design		Logistics data	
Product colour *	Black	Harmonized System (HS) code	85078000
Operational conditions		Other features	
Operating temperature (T-T)	0 - 40 °C	Battery type	VRLA
Storage temperature (T-T)	-15 - 40 °C	Interface	2x SmartSlot
Operating relative humidity (H-H)	0 - 95%	Output connections	1x Hard Wire 5-wire (3PH + N + G)
Storage relative humidity (H-H)	0 - 95%	Dimensions (WxDxH)	600 x 1070 x 1991 mm
		Output voltage note	380, 400/415
		Package dimensions (WxDxH)	848 x 1210 x 2140 mm



7330381057076



8592978149147

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.