
3M Privacy Filter for 23.6in Monitor, 16:9, PF236W9B

Brand : 3M

Product code: PF236W9B

Product name : Privacy Filter for 23.6in Monitor, 16:9, PF236W9B



- Effective "black out" privacy from side views outside the 60-degree viewing angle
- Durable privacy filter that can withstand hundreds of cleanings
- Helps reduce blue light, without distorting the natural color of your display.
- A reversible solution, 3M™ Privacy Filters offer a glossy option and a matte option that help reduce glare and fingerprints.
- 100% hand inspected for quality assurance.

Privacy Filter for 23.6in Monitor, 16:9, PF236W9B

3M Privacy Filter for 23.6in Monitor, 16:9, PF236W9B:

Achieve world-class privacy with 3M™ Privacy Filters, the leading name in screen solutions. Offers exceptional clarity and security while protecting screens from hazards without affecting performance. Make 3M your first line of defense against visual hackers, damage, glare, and more—at home, in the office, and everywhere you work.

Design	
Maximum screen size *	59.9 cm (23.6")
Suitable for *	Monitor
Type *	Frameless display privacy filter
Screen size HxW	522 x 294 mm
Display diagonal (metric)	59.9 cm
Filter colour	Black
Reversibility	Matte-to-Glossy
Product colour	Black

Features	
Display filter features *	Anti-glare
Display types supported *	LCD
Aspect ratio	16:9
Widescreen	✔
Scratch-resistant	✔
Protection features	Dust resistant, Scratch-resistant
Limits viewing angle	60°
Easy to clean	✔
Surface finish	Glossy / Matt
Screen format	Widescreen
Country of origin	United States
Easy to apply	✔
Durable screen protection	✔
Privacy filtering orientation	Landscape
Touchscreen compatible	✘
Installation type	Adhesive strip + Slide mount tab
Easy to remove	✔
Fingerprint resistant	✔
Blue light filter	✔

Features	
Compatibility	Samsung S24B350TL; Lenovo ThinkVision G24-10; LG UltraGear 24GN53A-B; ACER V246HQL; Lenovo V510z; LG UltraGear 24GL65B-B; ViewSonic VS15453; ViewSonic VA2403; ViewSonic VA2407H; Dell SE2417HG; Lenovo D24-10; Sceptre C248B-144RN; Samsung S24E650PL; ViewSonic VX2458-MHD; Lenovo C24-10; ViewSonic VG2433MH; ACER ED242QR; ASUS VP247NA; ViewSonic VA2452Sm; LG UltraGear 24GL600F; ASUS TUF Gaming VG24VQ; ViewSonic VA2446mh-LED; ACER XF240Q; LG UltraGear 24M47VQ

Weight & dimensions	
Width	522 mm
Height	294 mm
Weight	98 g

Packaging data	
Package width	552 mm
Package depth	5 mm
Package height	368 mm
Package weight	374 g

Other features	
Anti-reflective	✔
Special features	Compatible For Device With Raized Bezel
Compliance certificates	Trade Agreements Act (TAA)

Logistics data	
Pallet net height	121.9 cm
Pallet net length	121.9 cm
Pallet net width	106.7 cm

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date

Logistics data	
Pallet net weight	56.4 kg
Pallet weight (EU)	289.8 kg
Products per pallet (EU)	575 pc(s)
Harmonized System (HS) code	85299097
Pallet gross width	106.7 cm
Pallet gross length	121.9 cm
Pallet gross height	121.9 cm
Pallet gross weight	289.8 kg
Shipping (inner) case width	37.9 cm
Shipping (inner) case length	56.4 cm
Shipping (inner) case height	4.8 cm
Shipping (inner) case gross weight	2.38 kg
Shipping (inner) case net weight	490 g
Products per shipping (inner) case	5 pc(s)
Shipping (inner) case GTIN (EAN/UPC)	50051128797179




5712505749074



5706998662842



7426800830884




0777787389986



777787389986




5147841649250




0804067413557



804067413557




5711783915669



7123290427456





0051128797174

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date

051128797174

Catalog Object Cloud

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date