



APC Smart-UPS On-Line SRT Battery Pack for 5/6kVA Extended runtime model 192V

Brand : APC

Product code: SRT192BP

Product name : Smart-UPS On-Line SRT Battery Pack for 5/6kVA Extended runtime model 192V



Smart-UPS On-Line SRT Battery Pack for 5/6kVA Extended runtime model 192V

APC Smart-UPS On-Line SRT Battery Pack for 5/6kVA Extended runtime model 192V:

This APC Smart-UPS battery pack connected with SRT On-Line UPS, provides extended runtime to SRT mission critical applications. This 192V SRT extendable runtime battery pack is compatible with 5kVA/6kVA SRT Smart-UPS extended runtime models. Embedded monitoring at the cell, module, and cabinet level provides data of battery runtime and health. It is a lead-acid battery with a 2-year warranty. It is a lead-acid battery with a 2-year warranty. Its dimensions are 683mm (depth) x 432mm (height) x 130mm (width) and weighs 91.0kg. Ideal for Smart-UPS on-line mission critical applications. APC Smart-UPS On-Line SRT Battery Pack for 5/6kVA Extended runtime model 192V. Form factor: Rackmount, Product colour: Black. Battery technology: Lead acid, Battery voltage: 192 V. Compliance certificates: RoHS. Width: 130 mm, Depth: 682 mm, Height: 432 mm. Package width: 600 mm, Package depth: 1000 mm, Package height: 420 mm

Design		Certificates	
Form factor *	Rackmount	Compliance certificates	RoHS
Rack mounting	✓	Weight & dimensions	
Product colour	Black	Width	130 mm
Battery		Depth	682 mm
Battery technology	Lead acid	Height	432 mm
Battery voltage	192 V	Weight	91 kg
Operational conditions		Packaging content	
Operating temperature (T-T)	0 - 40 °C	Rack mount kit	✓
Storage temperature (T-T)	-15 - 45 °C	Packaging data	
Operating relative humidity (H-H)	0 - 95%	Package width	600 mm
Storage relative humidity (H-H)	0 - 95%	Package depth	1000 mm
Operating altitude	0 - 900 m	Package height	420 mm
Non-operating altitude	0 - 4500 m	Package weight	101.5 kg
		Logistics data	
		Total carbon footprint (kg of CO2e)	749.39



0731304301769



731304301769

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.